

KERN OBT 104

The modern compound microscope for teaching in your class room

KERN



Ocular diameter 23,2 mm

Objective

Objectives - Details	Objective Achromatic 10x / 0,25
	Objective Achromatic 4x / 0,1
	Objective Achromatic 40x / 0,65 spring
Objectives magnifications	4x / 10x / 40x

Illumination

Illuminance	Transmitted light
Illumination type transmitted light	LED
Illumination intensity transmitted light	1 W
Illumination dimmable	Transmitted light
Filter possible	✓
Aperture diaphragm	✓

Focussing

Field of view [Min]	0,45 mm
Field of view [Max]	4,5 mm
Fine drive minimum	0,0025 mm
Focusing mechanism	coaxial coarse and fine drive

Condensor

Condensor type	Abbe
----------------	------

Power Supply

Supplied power supply	Power supply & battery function (battery not included)
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO
Plug-in power supply / adapter for countries - optional	AUS UK US CH
Input voltage power supply / power [Max]	100 - 240 V
Power supply cable removable	removable
Input voltage device / power [Max]	5 V 1000 mA
Battery connection	Pad + Spring

Category

Brand	Optics
Product category	Microscope
Product group	Compound microscope
Product family	OBT-1

Construction

Dimension (W×D×H)	195×147×325 mm
Optical system	Finite
Tube type	Binocular
Tube angle of inclination	45°
Tube 360° rotation	✓
Contrasting methods	Bright field
Standard objectives	4x 10x 40x
Lens quality	achromatic
Nosepiece screw-in locations	4
Eyepieces fixed	✓
Interpupillary distance [Min]	48 mm
Interpupillary distance [Max]	75 mm
Diopter adjustment	one-sided
Diopter adjustment [Min]	-5
Diopter adjustment [Max]	5

Ocular

Ocular type	Eyepiece WF 10x / Ø 18mm
Ocular field width	WF
Eye point	Standard
Ocular magnifications	10x
Ocular visual field	18 mm

KERN OBT 104

KERN

The modern compound microscope for teaching in your class room

Environmental conditions

Storage temperature [Min]	-5 °C
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	400×280×195 mm
Shipping method	Parcel service
Net weight approx.	2,8 kg
Gross weight approx.	3,4 kg
Shipping weight	4,4 kg

Product information

GTIN/EAN number	4045761228979
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

