

VIEW4 LITE



2 days of use



Super Wide Angle
& Blur effect



Full screen display



2 days use. Triple camera.

Keep going with 2 days of power in a single charge on your View4 Lite! The smartphone brings you a long-life battery, a Super Wide Angle triple camera and ultra-large memory.

Available colours: ● Deep Blue ● Deep Gold ● Deep Green

CUSTOMISED ACCESSORIES

- **Smart Folio** with standing option to enjoy your content hands-free
- **Slim Clear Case** with hard back cover and flexible frame
- Ultra-resistant **Printed Tempered Glass** that protects your phone against scratches

Hauptmerkmale	
Mobilfunknetzwerke	4G LTE B1 (2100)/ B3 (1800)/ B5 (850) / B7 (2600)/ B8 (900) / B20 (800) / B28B(700) / B40 (2300) H+/3G+/3G HSPA+ 850/ 900/ 1900/ 2100 MHz GSM/GPRS/EDGE 850/900/1800/1900 MHz
Datenrate	FDD-LTE Category 4 DL 150 Mbps, UL 50 Mbps
Betriebssystem	Android™ 10
Prozessor	Mediatek 6762D A25, Octa-Core 1.8 GHz
Grafikkarte - GPU	IMG PowerVR GE8320
Dual SIM	2 Nano SIM
Design	Touch screen
Erhältlich in den Farben	Deep Blue, Deep Green, Deep Gold with Plastic finish
Abmessungen	167x 76.8x 8.45
Gewicht	174
Akku	4000 mAh Li-Po
Standby-Zeit	Up to 692h
Gesprächszeit	Up to 43.9h
Interner Speicher (ROM)	32GB
Arbeitsspeicher (RAM)	2GB
Speicher erweiterbar	Micro SD card up to 256GB
Beschleunigungssensor	Ja
Kompass (Magnetometer)	Ja
Annäherungssensor	Ja
SAR-Wert	Head : 0.538W/kg, Body : 1.582 W/kg, Limb : 2.503 W/Kg
Bildschirm	
Abmessungen	6.52
Typ	IPS Technology, 450 nits brightness
Farbe	16.7M
Auflösung	HD+ (1600 x 720 pixels), pixel density: 269 PPI
Multi touch	Ja
Konnektivität	
WLAN / Wi-Fi	802.11 b/g/n
Tethering & Mobiler Hotspot	USB, Bluetooth, Access Point Wi-Fi
Bluetooth Version	4.2
USB OTG	Ja
USB Anschluss	2.0
PC Synchronisation	Ja
Kopfhörerausgang	3.5mm jack
Foto & Video	
Kamera	Triple: 13MP (Main) + 2MP (Depth) + 5MP (114° Super Wide Angle)
Optionen	Face Beauty, Night mode, HDR, Time Lapse, Slow Motion, AI mode, Super Wide Angle, Bokeh mode, Google Lens, Live filter

Blitzlicht	Ja
Frontkamera	5MP
Digital Zoom	4x
Autofokus	No
Bildeditor	Ja
Weissabgleich	Auto, Incandescent, Daylight, Fluorescent, Cloudy
Videaufnahmen	1080p@30fps
Multimedia und Unterhaltung	
Stereo FM Radio	Ja
Audio Formate	MP3, Midi, AAC, AMR
Bild Formate	JPEG, GIF, PNG, BMP
Video Formate	3GPP, MP4 , 3GP, H.264
GPS	
GPS	Ja
A-GPS	Ja
Personalisierung	
Sprachen	English, French, Italian, German, Dutch, Spanish, Portuguese, Russian, Czech, Polish, Finnish, Hungarian, Arabic, Urdu, Persian, Danish, Norwegian, Swedish, Thai, Indonesian, Vietnamese, Turkish, Cyrillic Serbian, Latin Serbian, Slovenian, Macedonian, Croatian, Catalan, Basque, Romanian, Polish, Slovak, Ukrainian, Greek
Wiko features	Face Unlock, Wiko Launcher, One Handed Mode, Simple Mode, Smart Assist, Smart Action, Google Assistant Button
Google™ Mobile Service	
Google Apps	Ja
Packungsinhalt	
	Headset
Kurzanleitung	Google Assistant user guide
	Micro USB Kabel Netzteil Wiko Mobiltelefon
Änderung der technischen Daten vorbehalten. Der Zugriff auf Google™-Anwendungen kann je nach Land abweichen.	



Der SAR-Wert (spezifische Absorptionsrate) der Mobiltelefone, fasst den maximalen Expositionspegel an elektromagnetischen Wellen, für eine Nutzung am Ohr, in Zahlen zusammen. Die europäische Regelung verlangt, dass die SAR 2W/kg nicht übersteigt.
© Wiko. Alle Rechte vorbehalten. Wi-Fi ist eine Marke der Wi-Fi Alliance. Bluetooth ist eine Marke von Bluetooth SIG. Alle anderen Warenzeichen sind das Eigentum ihrer jeweiligen Betreiber