



Faro ricaricabile portatile per utilizzo in ambienti pericolosi  
Portable rechargeable lantern for use in hazardous locations  
Phare portable rechargeable pour utilisation en milieux dangereux  
Luz portátil recargable para uso en entornos peligrosos.  
Wiederaufladbare tragbare Lampe für den Einsatz in gefährlichen Umgebungen

SPOTEX



PACKING	INNER	MASTER
☐ / ☐	☐ pcs	☐ pcs
White box	2	8





## DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN

Codice / Item / Code / Código / Code	SPOTEX
Nome prodotto / product name / Nom du produit / Designación / Produktname	SPOTEX
Alimentazione / Power supply / Alimentation / Alimentación / Stromversorgung	230V ~ 50/60Hz, 9V --- 1000mA
Batteria / Battery / Batterie / Batería / Batterie	3.7V 1960mAh, Li-Ion (Type 18650)
Tempo di ricarica / Charging Time / Temps de recharge / Tiempo de carga / Ladezeit	6 hrs
Autonomia / Runtime / Autonomie / Autonomía / Leuchtdauer	100%: 4 hrs, 50%: 16 hrs, 20%: 50 hrs
Tecnologia della Luce / Light technology / Technologie de la lumière / Tecnología de iluminación / Leuchtentechnologie	LED CREE®-XP-G3
Potenza d'illuminazione (W) / (W) Power / Puissance (W) / Potencia (W) / Leuchtstärke (W)	5W
Consumo elettrico (W) / (W) Consumption / Consommation (W) / Consumo (W) / Verbrauch (W)	-
Lumen / Lumen / Lumen / Lumen / Lumen	300 Lm
Tipo di luce / Kelvin degrees / Degrés Kelvin / Temperatura de luz / Grad Kelvin	6500K
IRC / Colour rendering Index / Indice de rendu des couleurs / IRC / Farbwiedergabeindex	-
Fascio di luce / Light beam / Type de faisceau / Tipo de haz / Lichtstrahl	Focus light 30°
Portata / Range / Distance d'éclairage / Alcance alumbrado / Leuchtweite	334 m
Durata di vita del LED / LED Life time / Durée de vie des LED / Durada de vida del LED /	50.000 hrs
Massima intensità del fascio / Peak beam intensity / Intensité maximale du faisceau / Máxima intensidad / Abstrahlintensität	9732 cd
Dimmerabilità / Dimmable / Dimmable / Dimmer, regulador / Dimmereigenschaften	Yes (100% / 50% / 20%)
Numero di cicli on-off / On off cycles / Nr de cycles on-off / Numero de On-OFF / Ein-Aus Zyklen	-
Power factor / Power factor / Power factor / Power factor / Leistungsfaktor	-
Collegamenti / Connections / Connexions / Conexiones / Anschlüsse	-
Classe di isolamento / Insulation class / Classe isolation / Clase de aislamiento / Isolationsklasse	III
Cavo / Cable / Câble / Cable / Kabel	-
Materiale / Material / Materiau / Material / Material	PC + ABS
Grado di protezione / Protection degree / Degré de protection / Estanqueidad / Schutzgrad	IP64
Resistenza Meccanica / Mechanical resistance / Résistance Mécanique / Resistencia mecanica / Mechanische Widerstandsfähigkeit	-
Accessori / Accessories / Accessoires / Accesorios / Zubehör	Wall charging base, AC/DC Adaptor
Funzioni / Functions / Fonctions / Función / Funktionen	Light 100%, Light 50%, Light 20%, OFF
Garanzia / Guarantee / Garantie / Garantía	2 years

## DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN

	Width (mm)	Length (mm)	Height (mm)
<b>Dimensioni prodotto</b> / Product dimensions / Dimensions du produit / Dimensiones producto / Abmessungen Produkt	205	136	77
<b>Peso netto unità</b> / Unit net weight / Poids net de l'unité / Peso neto unidad/ Nettogewicht pro Einheit	g		
<b>Dimensioni prodotto imballato</b> / Packed dimensions / Dimensions du produit emballé / Abmessungen Umverpackung Dimensiones embalaje	Width (mm)	Length (mm)	Height (mm)
	297	174	142
<b>Peso prodotto imballato</b> / Weight of packaged product / Poids du produit emballé / Peso producto con embalaje / Gewicht mit Umverpackung	g		
<b>Dimensioni inner</b> / Inner dimensions / Dimensions de l'inner / Dimensiones embalaje / Abmessungen Inner	Width (cm)	Length (cm)	Height (cm)
<b>Peso lordo inner</b> / Inner gross weight / Poids brut de l'inner / Peso embalaje / Bruttogewicht Inner	Kg		
<b>Dimensioni display</b> / Display dimensions / Dimensions du présentoir / Dimensiones display/ Abmessungen Display	Width (cm)	Length (cm)	Height (cm)
<b>Peso lordo display</b> / Display gross weight / Poids brut du présentoir //Peso display - expositor / Bruttogewicht Display	Kg		
<b>Dimensioni Master</b> / Master gross dimensions / Dimensions du master / Dimensiones caja master / Abmessungen Master	Width (cm)	Length (cm)	Height (cm)
<b>Peso lordo master</b> / Master gross weight / Poids brut du master / Peso caja master / Bruttogewicht Master	Kg		
<b>Quanti pezzi su pallet 80x120</b> How many pieces per euro pallet / Combien de pièces par euro palettes? Cuantas piezas sobre paleta tamaño 80x120? / Wieviele Stücke pro Euro-Palette?			

	Class I Div 1&2 Grp ABCD / Class II Div 1&2 Grp EFG Class III / Temperature Code T4 IP64 File number: 261379
	Gas: II 1G Ex ia op is IIC T4 Ga (Zone 0) Mine: I M1 Ex ia op is I Ma SIRA 17 ATEX 2195X
IECEX	Gas: Ex ia op is IIC T4 Ga (Zone 0) Mine: Ex ia op is I Ma IECEX SIR 17.0042X
CE	0518

