

PANTHER

Torcia in alluminio ricaricabile LED 10W
 10W LED rechargeable aluminium flashlight
 Torche rechargeable LED 10W en aluminium
 Lanterna de metal LED 10W recargable
 Taschenlampe LED 10W wiederaufladbar



IMR90



PACKING	INNER	MASTER
/	pcs	pcs
Blister F4	6	48



DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN

Codice / Item / Code / Codigo / Code	IMR90
Nome prodotto / product name / Nom du produit / Designación / Produktname	PANTHER
Alimentazione / Power supply / Alimentation / Alimentación / Stromversorgung	5V == adaptor (not included)
Batteria / Battery / Batterie/ Bateria / Batterie	1 x CR18650, 3.7V, 2200mAh (Li-Ion) (included)
Tempo di ricarica / Charging Time / Temps de recharge / Tiempo de carga / Ladezeit	3 hrs
Autonomia / Runtime / Autonomie / Autonomía / Leuchtdauer	Light 100%: 3 hrs - Light 50%: 10 hrs
Tecnologia della Luce / Light technology / Technologie de la lumière / Tecnología de iluminación / Leuchtentechnologie	LED 10W CREE® XPL
Potenza d'illuminazione (W) / (W) Power / Puissance (W) / Potencia (W) / Leuchtstärke (W)	10W
Consumo elettrico (W) / (W) Consumption / Consommation (W) / Consumo (W) / Verbrauch (W)	-
Lumen / Lumen / Lumen / Lumen / Lumen	800 Lm
Tipo di luce / Kelvin degrees / Degrés Kelvin / Temperatura de luz / Grad Kelvin	-
IRC / Colour rendering Index / Indice de rendu des couleurs / IRC / Farbwiedergabeindex	-
Fascio di luce / Light beam / Type de faisceau / Tipo de haz / Lichtstrahl	Adjustable (zoom): 12° / 75°
Portata / Range / Distance d'éclairage / Alcance alumbrado / Leuchtweite	200 m
Durata di vita del LED / LED Life time / Durée de vie des LED / Durada de vida del LED / Lebensdauer LED	20.000hrs
Massima intensità del fascio / Peak beam intensity / Intensité maximale du faisceau / Máxima intensidad / Abstrahlintensität	-
Dimmerabilità / Dimmable / Dimmable / Dimmer, regulador / Dimmereigenschaften	100% / 50%
Numero di cicli on-off / On off cycles / Nr de cycles on-off / Numero de On-OFF / Ein-Aus Zyklen	-
Power factor / Power factor / Power factor / Power factor / Leistungsfaktor	-
Cavo / Cable / Câble / Cable / Kabel	-
Materiale / Material / Materiau / Material / Material	AL
Grado di protezione / Protection degree / Degré de protection / Estanqueidad / Schutzgrad	IPX4
Accessori inclusi / Accessories included / Accessoires fourni / Accesorios incluidos / Zubehör enthalten	Micro USB cable 50 cm + Folder + Battery
Funzioni / Functions / Fonctions / Función / Funktionen	
Dimensioni prodotto / Product dimensions / Dimensions du produit / Dimensiones producto / Abmessungen Produkt	Width x Height x Length: 360 x 138,5 mm
Dimensioni prodotto imballato / Packed dimensions / Dimensions du produit emballé / Dimensiones embalaje / Abmessungen Umverpackung	Width x Height x Length: 322 x 103 x 70 mm
Peso netto / Net Weight / Poids net / Peso neto / Gewicht netto	220 g
Peso prodotto imballato / Weight of packaged product / Poids du produit emballé / Peso producto con embalaje / Gewicht mit Umverpackung	266 g