



## SENTINEL

Lampada da testa LED CREE®  
 CREE® LED headlamp  
 Lampe frontale LED CREE®  
 Linterna de cabeza LED CREE®  
 Power Lichtstrahl: CREE® LED

ST426



PACKING	INNER	MASTER
/	pcs	pcs
Blister F5	6	48



### DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN

<b>Codice</b> / Item / Code / Codigo / Code	ST426
<b>Nome prodotto</b> / product name / Nom du produit / Designación / Produktname	SENTINEL
<b>Alimentazione</b> / Power supply / Alimentation / Alimentación / Stromversorgung	Li-ion Battery
<b>Batteria</b> / Battery / Batterie/ Batería / Batterie	700mAh 16340 Li-ion Battery (included)
<b>Tempo di ricarica</b> / Charging Time / Temps de recharge / Tiempo de carga / Ladezeit	2 hrs
<b>Autonomia</b> / Runtime / Autonomie / Autonomía / Leuchtdauer	>2 hrs (40%)
<b>Tecnologia della Luce</b> / Light technology / Technologie de la lumière / Tecnología de iluminación / Leuchtentechnologie	High power CREE® XPG3 LED
<b>Potenza d'illuminazione (W)</b> / (W) Power / Puissance (W) / Potencia (W) / Leuchtstärke (W)	6W
<b>Consumo elettrico (W)</b> / (W) Consumption / Consommation (W) / Consumo (W) / Verbrauch (W)	-
<b>Lumen</b> / Lumen / Lumen / Lumen / Lumen	600 Lm (100%)
<b>Tipo di luce</b> / Kelvin degrees / Degrés Kelvin / Temperatura de luz / Grad Kelvin	-
<b>IRC</b> / Colour rendering Index / Indice de rendu des couleurs / IRC / Farbwiedergabeindex	-
<b>Fascio di luce</b> / Light beam / Type de faisceau / Tipo de haz / Lichtstrahl	Diffuse
<b>Portata</b> / Range / Distance d'éclairage / Alcance alumbrado / Leuchtweite	90 m (100%)
<b>Durata di vita del LED</b> / LED Life time / Durée de vie des LED / Durada de vida del LED / Lebensdauer LED	25.000 hrs
<b>Massima intensità del fascio</b> / Peak beam intensity / Intensité maximale du faisceau / Máxima intensidad / Abstrahlintensität	2000 Cd
<b>Dimmerabilità</b> / Dimmable / Dimmable / Dimmer, regulador / Dimmereigenschaften	-
<b>Numero di cicli on-off</b> / On off cycles / Nr de cycles on-off / Numero de On-OFF / Ein-Aus Zyklen	-
<b>Power factor</b> / Power factor / Power factor / Power factor / Leistungsfaktor	-
<b>Cavo</b> / Cable / Câble / Cable / Kabel	USB induction charging cable 50 cm
<b>Materiale</b> / Material / Materiau / Material / Material	AL
<b>Grado di protezione</b> / Protection degree / Degré de protection / Estanqueidad / Schutzgrad	IPX4
<b>Resistenza Meccanica</b> / Mechanical resistance / Résistance Mécanique / Resistencia mecanica / Mechanische Widerstandsfähigkeit	-
<b>Accessori inclusi</b> / Accessories included / Accessoires fourni / Accesorios incluidos / Zubehör enthalten	Clip, Li-ion battery, USB induction charging cable, headband
<b>Funzioni</b> / Functions / Fonctions / Función / Funktionen	- 1° CLICK: light 40% - 2° CLICK: light 10% - 3° CLICK: OFF - LONG CLICK: light 100% (600 lm) for 40 seconds - 2 fast CLICKS: Strobe

<b>DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN</b>	
<b>Dimensioni prodotto</b> / Product dimensions / Dimensions du produit / Dimensiones producto / Abmessungen Produkt	Width x Height x Length: 23 ø x 73 mm
<b>Peso netto unità</b> / Unit net weight / Poids net de l'unité / Peso neto unidad/ Nettogewicht pro Einheit	95 g
<b>Dimensioni prodotto imballato</b> / Packed dimensions / Dimensions du produit emballé / Abmessungen Umverpackung Dimensiones embalaje	Width x Height x Length:
<b>Peso prodotto imballato</b> / Weight of packaged product / Poids du produit emballé / Peso producto con embalaje / Gewicht mit Umverpackung	
<b>Dimensioni inner</b> / Inner dimensions / Dimensions de l'inner / Dimensiones embalaje / Abmessungen Inner	
<b>Peso lordo inner</b> / Inner gross weight / Poids brut de l'inner / Peso embalaje / Bruttogewicht Inner	
<b>Dimensioni display</b> / Display dimensions / Dimensions du présentoir / Dimensiones display/ Abmessungen Display	
<b>Peso lordo display</b> / Display gross weight / Poids brut du présentoir //Peso display - expositor / Bruttogewicht Display	
<b>Dimensioni Master</b> / Master gross dimensions / Dimensions du master / Dimensiones caja master / Abmessungen Master	
<b>Peso lordo master</b> / Master gross weight / Poids brut du master / Peso caja master / Bruttogewicht Master	
<b>Quanti master su un layer 80x120</b> / How many master cartons per 80x120 cm layers? / Combien de masters par couches 80x120cm? / Cuantas cajas master por capa tamaño 80x120 / Master Kartons pro 80 x 120 cm Fläche / Schicht	
<b>Quanti layer per pallet</b> / How many layers per pallet? / Combien de couches par palettes? / Cuantas capas por paleta / / Wie viele Schichten pro Palette? /	
<b>Quanti master su pallet 80x120</b> / How many master cartons per euro pallet? / Combien de master cartons par euro palettes? / / Cuantas cajas master sobre paleta tamaño 80x120 / Wieviele Master Kartons pro Euro-Palette?	