



TRAINSPOTTING

Faro ricaricabile a LED 20 WATT CREE®
 Rechargeable 20W CREE® LED spotlight
 Phare rechargeable 20 Watt à LED CREE®
 Projector recargable 20WATT LED CREE®
 Wiederaufladbare 20W CREE(R)LED Handleuchte

NEW!
 with **ANTI
 BLACK-OUT**
 function

POWER BANK FUNCTION



RED REAR LIGHT



TRIPOD ADAPTOR



R920



PACKING	INNER	MASTER
/	pcs	pcs
Colour box	-	4



DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN

Codice / Item / Code / Codigo / Code	R920
Nome prodotto / product name / Nom du produit / Designación / Produktname	TRAINSPOTTING
Alimentazione / Power supply / Alimentation / Alimentación / Stromversorgung	230V ~ 50Hz / 7,5V === 350mA
Batteria / Battery / Batterie/ Bateria / Batterie	Pb 6V 4 Ah
Tempo di ricarica / Charging Time / Temps de recharge / Tiempo de carga / Ladezeit	14 hrs
Autonomia / Runtime / Autonomie / Autonomía / Leuchtdauer	HI beam (100%): 3hrs LOW beam (50%) 8 hrs
Tecnologia della Luce / Light technology / Technologie de la lumière / Tecnología de iluminación / Leuchtentechnologie	CREE® XHP LED
Potenza d'illuminazione (W) / (W) Power / Puissance (W) / Potencia (W) / Leuchtstärke (W)	20W
Consumo elettrico (W) / (W) Consumption / Consommation (W) / Consumo (W) / Verbrauch (W)	-
Lumen / Lumen / Lumen / Lumen / Lumen	1600 Lm
Tipo di luce / Kelvin degrees / Degrés Kelvin / Temperatura de luz / Grad Kelvin	-
IRC / Colour rendering Index / Indice de rendu des couleurs / IRC / Farbwiedergabeindex	-
Fascio di luce / Light beam / Type de faisceau / Tipo de haz / Lichtstrahl	Focus Light
Portata / Range / Distance d'éclairage / Alcance alumbrado / Leuchtweite	>1500 m
Durata di vita del LED / LED Life time / Durée de vie des LED / Durada de vida del LED / Lebensdauer LED	30.000 hrs
Massima intensità del fascio / Peak beam intensity / Intensité maximale du faisceau / Máxima intensidad / Abstrahlintensität	-
Dimmerabilità / Dimmable / Dimmable / Dimmer, regulador / Dimmereigenschaften	-
Numero di cicli on-off / On off cycles / Nr de cycles on-off / Numero de On-OFF / Ein-Aus Zyklen	-
Power factor / Power factor / Power factor / Power factor / Leistungsfaktor	-
Cavo / Cable / Câble / Cable / Kabel	-
Materiale / Material / Materiau / Material / Material	ABS/PP
Grado di protezione / Protection degree / Degré de protection / Estanqueidad / Schutzgrad	IP43
Accessori inclusi / Accessories included / Accessoires fourni / Accesorios incluidos / Zubehör enthalten	Carry strap, 12V Car adaptor, Tripod adaptor, 220V Home adaptor, USB output for powerbank function
Funzioni / Functions / Fonctions / Función / Funktionen	Red blink / Powerbank function
Dimensioni prodotto / Product dimensions / Dimensions du produit / Dimensiones producto / Abmessungen Produkt	Width x Height x Length: 205 x 175 x 185 mm
Dimensioni prodotto imballato / Packed dimensions / Dimensions du produit emballé / Dimensiones embalaje / Abmessungen Umverpackung	Width x Height x Length: 220 x 195 x 205 mm
Peso netto / Net Weight / Poids net / Peso neto / Gewicht netto	1685 g
Peso prodotto imballato / Weight of packaged product / Poids du produit emballé / Peso producto con embalaje / Gewicht mit Umverpackung	1875 g