



PROLED

Penlite LED con clip
LED penlite with clip
Penlite LED avec clip
Linterna boligrafo LED
Penlite LED mit Clip



IS314



PACKING	INNER	MASTER
Blister F2	pcs	pcs
	6	48



DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN

Codice / Item / Code / Codigo / Code	IS314
Nome prodotto / product name / Nom du produit / Designación / Produktname	PROLED
Alimentazione / Power supply / Alimentation / Alimentación / Stromversorgung	Dry batteries
Batteria / Battery / Batterie/ Batería / Batterie	3 X AAA (not included)
Tempo di ricarica / Charging Time / Temps de recharge / Tiempo de carga / Ladezeit	-
Autonomia / Runtime / Autonomie / Autonomía / Leuchtdauer	Panel: 7 hrs / Flashlight: 15 hrs
Tecnologia della Luce / Light technology / Technologie de la lumière / Tecnología de iluminación / Leuchtentechnologie	2W COB +1W High power LED
Potenza d'illuminazione (W) / (W) Power / Puissance (W) / Potencia (W) / Leuchtstärke (W)	
Consumo elettrico (W) / (W) Consumption / Consommation (W) / Consumo (W) / Verbrauch (W)	
Lumen / Lumen / Lumen / Lumen / Lumen	150 Lumen
Tipo di luce / Kelvin degrees / Degrés Kelvin / Temperatura de luz / Grad Kelvin	
IRC / Colour rendering Index / Indice de rendu des couleurs / IRC / Farbwiedergabeindex	
Fascio di luce / Light beam / Type de faisceau / Tipo de haz / Lichtstrahl	Diffuse + Focus
Portata / Range / Distance d'éclairage / Alcance alumbrado / Leuchtweite	15 mt
Durata di vita del LED / LED Life time / Durée de vie des LED / Durada de vida del LED /	20.000 hrs
Massima intensità del fascio / Peak beam intensity / Intensité maximale du faisceau / Máxima intensidad / Abstrahlintensität	
Dimmerabilità / Dimmable / Dimmable / Dimmer, regulador / Dimmereigenschaften	
Numero di cicli on-off / On off cycles / Nr de cycles on-off / Numero de On-OFF / Ein-Aus Zyklen	
Power factor / Power factor / Power factor / Power factor / Leistungsfaktor	
Cavo / Cable / Câble / Cable / Kabel	
Materiale / Material / Materiau / Material / Material	ABS
Grado di protezione / Protection degree / Degré de protection / Estanqueidad / Schutzgrad	
Resistenza Meccanica / Mechanical resistance / Résistance Mécanique / Resistencia mecanica / Mechanische Widerstandsfähigkeit	
Accessori / Accessories / Accessoires / Accesorios / Zubehör	
Funzioni / Functions / Fonctions / Función / Funktionen	
Dimensioni prodotto / Product dimensions / Dimensions du produit / Dimensiones producto / Abmessungen Produkt	Width x Height x Length: 170 x 30 x 15 mm
Dimensioni prodotto imballato / Packed dimensions / Dimensions du produit emballé / Dimensiones embalaje / Abmessungen Umverpackung	Width x Height x Length:
Peso netto / Net Weight / Poids net / Peso neto / Gewicht netto	40 g
Peso prodotto imballato / Weight of packaged product / Poids du produit emballé / Peso producto con embalaje / Gewicht mit Umverpackung	