



DAVY

Lampada da lavoro LED ricaricabile multifunzione
LED Rechargeable multifunction work lamp
Lampe de travail LED multifonction rechargeable
Lámpara para taller LED recargable
Multifunktionale aufladbare LED Arbeitsleuchte

IR471




PACKING	INNER	MASTER
	pcs	pcs
Display: 6 pces of Blister F5	6	48



DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN

Codice / Item / Code / Código / Code	IR471
Nome prodotto / product name / Nom du produit / Designación / Produktname	DAVY
Alimentazione / Power supply / Alimentation / Alimentación / Stromversorgung	5V === 1000mA
Batteria / Battery / Batterie/ Batería	Li-Ion 3,7V 1200mAh (18650) (Included)
Tempo di ricarica / Charging Time / Temps de recharge / Tiempo de carga	-
Autonomia / Runtime / Autonomie / Autonomía	2,5 hrs
Tecnologia della Luce / Light technology / Technologie de la lumière / Tecnología de iluminación / Leuchtentechnologie	3W COB LED (panel) 3W LED (torch)
Potenza d'illuminazione (W) / (W) Power / Puissance (W) / Potencia (W) / Leuchtstärke (W)	3W (panel) 3W (torch)
Consumo elettrico (W) / (W) Consumption / Consommation (W) / Consumo (W) / Verbrauch (W)	-
Lumen / Lumen / Lumen / Lumen / Lumen	Panel: 150 Lm Torch: 60 Lm
Tipo di luce / Kelvin degrees / Degrés Kelvin / Temperatura de luz / Grad Kelvin	6000K
IRC / Colour rendering Index / Indice de rendu des couleurs / IRC / Farbwiedergabeindex	-
Fascio di luce / Light beam / Type de faisceau / Tipo de haz / Lichtstrahl	-
Portata / Range / Distance d'éclairage / Alcance alumbrado / Leuchtweite	20 m
Durata di vita del LED / LED Life time / Durée de vie des LED / Durada de vida del LED / Lebensdauer LED	Diffuse + Focus Light
Massima intensità del fascio / Peak beam intensity / Intensité maximale du faisceau / Máxima intensidad / Abstrahlintensität	-
Dimmerabilità / Dimmable / Dimmable / Dimmer, regulador / Dimmereigenschaften	-
Numero di cicli on-off / On off cycles / Nr de cycles on-off / Numero de On-OFF / Ein-Aus Zyklen	-
Power factor / Power factor / Power factor / Power factor / Leistungsfaktor	-
Cavo / Cable / Câble / Cable / Kabel	-
Materiale / Material / Materiau / Material / Material	ABS + PC + TPR
Grado di protezione / Protection degree / Degré de protection / Estanqueidad / Schutzgrad	IP44
Resistenza Meccanica / Mechanical resistance / Résistance Mécanique / Resistencia mecanica / Mechanische Widerstandsfähigkeit	-
Accessori inclusi / Accessories included / Accessoires fourni / Accesorios incluidos / Zubehör enthalten	50 cm micro USB cable, Hook, Magnet
Funzioni / Functions / Fonctions / Función / Funktionen	-

DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN

Dimensioni prodotto / Product dimensions / Dimensions du produit / Dimensiones producto / Abmessungen Produkt	Width (mm)	Length (mm)	Height (mm)
	152	38	20
Peso netto unità / Unit net weight / Poids net de l'unité / Peso neto unidad/ Nettogewicht pro Einheit	0,140 Kg		
Dimensioni prodotto imballato / Packed dimensions / Dimensions du produit emballé / Abmessungen Umverpackung Dimensiones embalaje	Width (mm)	Length (mm)	Height (mm)
	100	34	310
Peso prodotto imballato / Weight of packaged product / Poids du produit emballé / Peso producto con embalaje / Gewicht mit Umverpackung	0,170 Kg		
Dimensioni inner / Inner dimensions / Dimensions de l'inner / Dimensiones embalaje / Abmessungen Inner	Width (cm)	Length (cm)	Height (cm)
	25,5	25,5	34
Peso lordo inner / Inner gross weight / Poids brut de l'inner / Peso embalaje / Bruttogewicht Inner	2,75 Kg		
Dimensioni display / Display dimensions / Dimensions du présentoir / Dimensiones display/ Abmessungen Display	Width (cm)	Length (cm)	Height (cm)
	23,7	12,5	32,5
Peso lordo display / Display gross weight / Poids brut du présentoir //Peso display - expositor / Bruttogewicht Display	1,29 Kg		
Dimensioni Master / Master gross dimensions / Dimensions du master / Dimensiones caja master / Abmessungen Master	Width (cm)	Length (cm)	Height (cm)
	54,5	53,5	36,5
Peso lordo master / Master gross weight / Poids brut du master / Peso caja master / Bruttogewicht Master	12,38 Kg		
Quanti pezzi su pallet 80x120 How many pieces per euro pallet / Combien de pièces par euro palettes? Cuantas piezas sobre paleta tamaño 80x120? / Wieviele Stücke pro Euro-Palette?			576

