



Rechargeable



MAGNET

HOOK



KUBRIK

Lampada da lavoro LED ricaricabile multifunzione
LED rechargeable multifunction work lamp
Lampe de travail LED rechargeable multifonctions
Lampara de trabajo multifunción LED recargable
Multifunktionale aufladbare LED Arbeitsleuchte

IR439




PACKING	INNER	MASTER
Blister F6	6	48



DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN

Codice / Item / Code / Código / Code	IR439
Nome prodotto / product name / Nom du produit / Designación / Produktname	KUBRIK
Alimentazione / Power supply / Alimentation / Alimentación / Stromversorgung	5V --- 1000A max
Batteria / Battery / Batterie/ Batería / Batterie	Li-Ion 3,7V 2000mAh (18650) (Included)
Tempo di ricarica / Charging Time / Temps de recharge / Tiempo de carga / Ladezeit	8 hrs
Autonomia / Runtime / Autonomie / Autonomía / Leuchtdauer	3 hrs (panel) 6 hrs (torch)
Tecnologia della Luce / Light technology / Technologie de la lumière / Tecnología de iluminación / Leuchtentechnologie	5W COB LED (panel) 3W High power LED (torch)
Potenza d'illuminazione (W) / (W) Power / Puissance (W) / Potencia (W) / Leuchtstärke (W)	5W
Consumo elettrico (W) / (W) Consumption / Consommation (W) / Consumo (W) / Verbrauch (W)	-
Lumen / Lumen / Lumen / Lumen / Lumen	Panel: 350 Lm Torch: 150 Lm
Tipo di luce / Kelvin degrees / Degrés Kelvin / Temperatura de luz / Grad Kelvin	6000K
IRC / Colour rendering Index / Indice de rendu des couleurs / IRC / Farbwiedergabeindex	-
Fascio di luce / Light beam / Type de faisceau / Tipo de haz / Lichtstrahl	Diffuse Light + focus
Portata / Range / Distance d'éclairage / Alcance alumbrado / Leuchtweite	20m
Durata di vita del LED / LED Life time / Durée de vie des LED / Durada de vida del LED /	20.000 hrs
Massima intensità del fascio / Peak beam intensity / Intensité maximale du faisceau / Máxima intensidad / Abstrahlintensität	-
Dimmerabilità / Dimmable / Dimmable / Dimmer, regulador / Dimmereigenschaften	NO
Cavo / Cable / Câble / Cable / Kabel	-
Materiale / Material / Materiau / Material / Material	PC + AL
Grado di protezione / Protection degree / Degré de protection / Estanqueidad / Schutzgrad	IP42
Resistenza Meccanica / Mechanical resistance / Résistance Mécanique / Resistencia mecanica / Mechanische Widerstandsfähigkeit	-
Accessori / Accessories / Accessoires / Accesorios / Zubehör	50 cm USB cable
Funzioni / Functions / Fonctions / Función / Funktionen	-
Garanzia / Guarantee / Garantie / Garantía	2 years

DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN

	Width (mm)	Length (mm)	Height (mm)
Dimensioni prodotto / Product dimensions / Dimensions du produit / Dimensiones producto / Abmessungen Produkt	150 (folded size) 250 (expended size)	37	30
Peso netto unità / Unit net weight / Poids net de l'unité / Peso neto unidad/ Nettogewicht pro Einheit	g		
Dimensioni prodotto imballato / Packed dimensions / Dimensions du produit emballé / Abmessungen Umverpackung Dimensiones embalaje	Width (mm)	Length (mm)	Height (mm)
Peso prodotto imballato / Weight of packaged product / Poids du produit emballé / Peso producto con embalaje / Gewicht mit Umverpackung	g		
Dimensioni inner / Inner dimensions / Dimensions de l'inner / Dimensiones embalaje / Abmessungen Inner	Width (cm)	Length (cm)	Height (cm)
Peso lordo inner / Inner gross weight / Poids brut de l'inner / Peso embalaje / Bruttogewicht Inner	Kg		
Dimensioni display / Display dimensions / Dimensions du présentoir / Dimensiones display/ Abmessungen Display	Width (cm)	Length (cm)	Height (cm)
Peso lordo display / Display gross weight / Poids brut du présentoir //Peso display - expositor / Bruttogewicht Display	Kg		
Dimensioni Master / Master gross dimensions / Dimensions du master / Dimensiones caja master / Abmessungen Master	Width (cm)	Length (cm)	Height (cm)
Peso lordo master / Master gross weight / Poids brut du master / Peso caja master / Bruttogewicht Master	Kg		
Quanti pezzi su pallet 80x120 How many pieces per euro pallet / Combien de pièces par euro palettes? Cuantas piezas sobre paleta tamaño 80x120? / Wieviele Stücke pro Euro-Palette?			



Le immagini sono fornite a solo scopo illustrativo e non costituiscono elemento contrattuale. Velamp Industries S.r.l. si riserva di apportare, in qualsiasi momento, ogni modifica ritenuta necessaria.
 All images are for illustrative purposes only and do not constitute a contractual element. Velamp Industries S.r.l. reserves the right to apply any changes it requires.
 Los imágenes tienen fin ilustrativa y no constituyen elementos contractuales. Velamp Industries S.r.l. se reserva el derecho a efectuar en cualquier momento y sin previo aviso las modificaciones que considere oportunas.