



HORNET 2

Faro LED ricaricabile
Rechargeable LED spotlight
Phare LED rechargeable
Projector rechargeable LED
Handleuchte LED wiederaufladbar



IR558



PACKING	INNER	MASTER
	pcs	pcs
Colour box	6	6



INCLUSI/INCLUDED/INCLUS



DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN

Codice / Item / Code / Código / Code	IR558
Nome prodotto / product name / Nom du produit / Designación / Produktname	HORNET 2
Alimentazione / Power supply / Alimentation / Alimentación / Stromversorgung	230-240V ~ 50Hz / 5V 200mA
Batteria / Battery / Batterie/ Batería / Batterie	Pb 4V 2Ah
Tempo di ricarica / Charging Time / Temps de recharge / Tiempo de carga / Ladezeit	8 hrs
Autonomia / Runtime / Autonomie / Autonomía / Leuchtdauer	Spotlight mode: 2 ore / hours Crown Light mode: 2 ore / hours
Tecnologia della Luce / Light technology / Technologie de la lumière / Tecnología de iluminación / Leuchtentechnologie	High Power LED + COB LED
Potenza d'illuminazione (W) / (W) Power / Puissance (W) / Potencia (W) / Leuchtstärke (W)	5W (High power) + 3,5W (COB LED)
Consumo elettrico (W) / (W) Consumption / Consommation (W) / Consumo (W) / Verbrauch (W)	
Lumen / Lumen / Lumen / Lumen / Lumen	350 Lm (High power) + 300 Lm (COB LED)
Tipo di luce / Kelvin degrees / Degrés Kelvin / Temperatura de luz / Grad Kelvin	
IRC / Colour rendering Index / Indice de rendu des couleurs / IRC / Farbwiedergabeindex	
Fascio di luce / Light beam / Type de faisceau / Tipo de haz / Lichtstrahl	Focus + Diffuse
Portata / Range / Distance d'éclairage / Alcance alumbrado / Leuchtweite	400 m
Durata di vita del LED / LED Life time / Durée de vie des LED / Durada de vida del LED /	20.000 hrs
Massima intensità del fascio / Peak beam intensity / Intensité maximale du faisceau / Máxima intensidad / Abstrahlintensität	-
Dimmerabilità / Dimmable / Dimmable / Dimmer, regulador / Dimmereigenschaften	-
Numero di cicli on-off / On off cycles / Nr de cycles on-off / Numero de On-OFF / Ein-Aus Zyklen	-
Power factor / Power factor / Power factor / Power factor / Leistungsfaktor	-
Cavo / Cable / Câble / Cable / Kabel	-
Materiale / Material / Matériau / Material / Material	PP
Grado di protezione / Protection degree / Degré de protection / Estanqueidad / Schutzgrad	IP44
Resistenza Meccanica / Mechanical resistance / Résistance Mécanique / Resistencia mecanica / Mechanische Widerstandsfähigkeit	
Accessori / Accessories / Accessoires / Accesorios / Zubehör	
Funzioni / Functions / Fonctions / Función / Funktionen	Home adaptor + car adaptor + Carry strap
Dimensioni prodotto / Product dimensions / Dimensions du produit / Dimensiones producto / Abmessungen Produkt	Width x Height x Length: 178 x 105 x 140 mm
Dimensioni prodotto imballato / Packed dimensions / Dimensions du produit emballé / Dimensiones embalaje / Abmessungen Umverpackung	Width x Height x Length: 184 x 156 x 115 mm
Peso netto / Net Weight / Poids net / Peso neto / Gewicht netto	600 g
Peso prodotto imballato / Weight of packaged product / Poids du produit emballé / Peso producto con embalaje / Gewicht mit Umverpackung	695 g