



10W

600 LUMEN



## THE EXPANDABLE

Proiettore ricaricabile LED  
LED rechargeable floodlight  
Projecteur LED rechargeable  
Projector LED recargable  
Baustrahler LED wiederaufladbar

IR882




PACKING	INNER	MASTER
/	pcs	pcs
Colour box	6	18



### DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN

Codice / Item / Code / Código / Code	IR882
Nome prodotto / product name / Nom du produit / Designación / Produktname	THE EXPANDABLE
Alimentazione / Power supply / Alimentation / Alimentación / Stromversorgung	AC/DC adaptor 100-240V ~ 50Hz / 5V --- 1000mA (included)
Batteria / Battery / Batterie/ Batería / Batterie	3,7V 2Ah Li-ion (Type 18650) not replaceable
Tempo di ricarica / Charging Time / Temps de recharge / Tiempo de carga / Ladezeit	12 hrs
Autonomia / Runtime / Autonomie / Autonomía / Leuchtdauer	2 hrs
Tecnologia della Luce / Light technology / Technologie de la lumière / Tecnología de iluminación / Leuchtentechnologie	SMD LED
Potenza d'illuminazione (W) / (W) Power / Puissance (W) / Potencia (W) / Leuchtstärke (W)	10W
Consumo elettrico (W) / (W) Consumption / Consommation (W) / Consumo (W) / Verbrauch (W)	-
Lumen / Lumen / Lumen / Lumen / Lumen	600 Lm
Tipo di luce / Kelvin degrees / Degrés Kelvin / Temperatura de luz / Grad Kelvin	6500K
IRC / Colour rendering Index / Indice de rendu des couleurs / IRC / Farbwiedergabeindex	-
Fascio di luce / Light beam / Type de faisceau / Tipo de haz / Lichtstrahl	Diffuse 100°
Portata / Range / Distance d'éclairage / Alcance alumbrado / Leuchtweite	-
Durata di vita del LED / LED Life time / Durée de vie des LED / Durada de vida del LED /	25.000 hrs
Massima intensità del fascio / Peak beam intensity / Intensité maximale du faisceau / Máxima intensidad / Abstrahlintensität	-
Dimmerabilità / Dimmable / Dimmable / Dimmer, regulador / Dimmereigenschaften	NO
Numero di cicli on-off / On off cycles / Nr de cycles on-off / Numero de On-OFF / Ein-Aus Zyklen	-
Power factor / Power factor / Power factor / Power factor / Leistungsfaktor	-
Collegamenti / Connections / Connexions / Conexiones / Anschlüsse	-
Classe di isolamento / Insulation class / Classe isolation / Clase de aislamiento / Isolationsklasse	III
Cavo / Cable / Câble / Cable / Kabel	-
Materiale / Material / Materiau / Material / Material	AL+ PP
Grado di protezione / Protection degree / Degré de protection / Estandeidad / Schutzgrad	IP65
Resistenza Meccanica / Mechanical resistance / Résistance Mécanique / Resistencia mecanica / Mechanische Widerstandsfähigkeit	-
Accessori / Accessories / Accessoires / Accesorios / Zubehör	Home adaptor + 1 m USB cable
Funzioni / Functions / Fonctions / Función / Funktionen	-
Garanzia / Guarantee / Garantie / Garantía	2 years

**DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN**

<b>Dimensioni prodotto</b> / Product dimensions / Dimensions du produit / Dimensiones producto / Abmessungen Produkt	Width (mm)	Length (mm)	Height (mm)
	205	63	225
<b>Peso netto unità</b> / Unit net weight / Poids net de l'unité / Peso neto unidad/ Nettogewicht pro Einheit	g		
<b>Dimensioni prodotto imballato</b> / Packed dimensions / Dimensions du produit emballé / Abmessungen Umverpackung Dimensiones embalaje	Width (mm)	Length (mm)	Height (mm)
	210	66	230
<b>Peso prodotto imballato</b> / Weight of packaged product / Poids du produit emballé / Peso producto con embalaje / Gewicht mit Umverpackung	g		
<b>Dimensioni inner</b> / Inner dimensions / Dimensions de l'inner / Dimensiones embalaje / Abmessungen Inner	Width (cm)	Length (cm)	Height (cm)
<b>Peso lordo inner</b> / Inner gross weight / Poids brut de l'inner / Peso embalaje / Bruttogewicht Inner	Kg		
<b>Dimensioni display</b> / Display dimensions / Dimensions du présentoir / Dimensiones display/ Abmessungen Display	Width (cm)	Length (cm)	Height (cm)
<b>Peso lordo display</b> / Display gross weight / Poids brut du présentoir //Peso display - expositor / Bruttogewicht Display	Kg		
<b>Dimensioni Master</b> / Master gross dimensions / Dimensions du master / Dimensiones caja master / Abmessungen Master	Width (cm)	Length (cm)	Height (cm)
<b>Peso lordo master</b> / Master gross weight / Poids brut du master / Peso caja master / Bruttogewicht Master	Kg		
<b>Quanti pezzi su pallet 80x120</b> How many pieces per euro pallet / Combien de pièces par euro palettes? Cuantas piezas sobre paleta tamaño 80x120? / Wieviele Stücke pro Euro-Palette?			



Le immagini sono fornite a solo scopo illustrativo e non costituiscono elemento contrattuale. Velamp Industries S.L. si riserva il diritto di apportare, in qualsiasi momento, ogni modifica ritenuta necessaria.  
 All images are for illustrative purposes only and do not constitute a contractual element. Velamp Industries S.L. reserves the right to make any changes it requires.  
 Los indigres tienen fin ilustrativo y no constituyen elementos contractuales. Velamp Industries S.L. se reserva el derecho a efectuar en cualquier momento y sin previo aviso las modificaciones que considere oportunas.