



**2X
20W**

**2X
1600
LUMEN**
EQUIVALENT TO
200W
HALOGEN

**6500K
COLD LIGHT**

Intertek



**3 mt
CABLE**

**176 cm
max**

**81 cm
min**

TWIN HEAD

Luce da lavoro LED 2 x 20W SMD + treppiede
2 x 20W SMD LED worklight + tripod
Lumière de travail LED 2 x 20W + trépied
Projector 2 x 20W LED SMD + tripode
LED-Arbeitslampe 2 x 20W + Stativ

IS747-3



PACKING	INNER	MASTER
/	pcs	pcs
Colour box	-	4




DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN

Codice / Item / Code / Código / Code	IS747-3
Nome prodotto / product name / Nom du produit / Designación / Produktname	TWIN HEAD
Alimentazione / Power supply / Alimentation / Alimentación / Stromversorgung	220-240V ~ 50/60 Hz
Tecnologia della Luce / Light technology / Technologie de la lumière / Tecnología de iluminación / Leuchtentechnologie	2835 SMD LED
Potenza d'illuminazione (W) / (W) Power / Puissance (W) / Potencia (W) / Leuchtstärke (W)	2 x 20W
Consumo elettrico (W) / (W) Consumption / Consommation (W) / Consumo (W) / Verbrauch (W)	40W
Lumen / Lumen / Lumen / Lumen / Lumen	2 x 1600 Lm
Tipo di luce / Kelvin degrees / Degrés Kelvin / Temperatura de luz / Grad Kelvin	6500K
IRC / Colour rendering Index / Indice de rendu des couleurs / IRC / Farbwiedergabeindex	>65 Ra
Fascio di luce / Light beam / Type de faisceau / Tipo de haz / Lichtstrahl	Diffuse 100°
Portata / Range / Distance d'éclairage / Alcance alumbrado / Leuchtweite	-
Durata di vita del LED / LED Life time / Durée de vie des LED / Durada de vida del LED / Lebensdauer LED	25.000 hrs
Massima intensità del fascio / Peak beam intensity / Intensité maximale du faisceau / Máxima intensidad / Abstrahlintensität	-
Dimmerabilità / Dimmable / Dimmable / Dimmer, regulador / Dimmereigenschaften	NO
Numero di cicli on-off / On off cycles / Nr de cycles on-off / Numero de On-OFF / Ein-Aus Zyklen	15.000
Power factor / Power factor / Power factor / Power factor / Leistungsfaktor	> 0.5
Cavo / Cable / Câble / Cable / Kabel	3 m H05RN-F 3G1.0mm ²
Materiale / Material / Materiau / Material / Material	Aluminium + ABS
Grado di protezione / Protection degree / Degré de protection / Estandeidad / Schutzgrad	IP65
Resistenza Meccanica / Mechanical resistance / Résistance Mécanique / Resistencia mecanica / Mechanische Widerstandsfähigkeit	-
Accessori inclusi / Accessories included / Accessoires fourni / Accesorios incluidos / Zubehör enthalten	-
Funzioni / Functions / Fonctions / Función / Funktionen	-

DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN

Dimensioni prodotto / Product dimensions / Dimensions du produit / Dimensiones producto / Abmessungen Produkt	Width x Height x Length: 1760 x 740 x 740 mm
Peso netto unità / Unit net weight / Poids net de l'unité / Peso neto unidad/ Nettogewicht pro Einheit	
Dimensioni prodotto imballato / Packed dimensions / Dimensions du produit emballé / Abmessungen Umverpackung / Dimensiones embalaje	Width x Height x Length: 220 x 170 x 680 mm
Peso prodotto imballato / Weight of packaged product / Poids du produit emballé / Peso producto con embalaje / Gewicht mit Umverpackung	g
Dimensioni inner / Inner dimensions / Dimensions de l'inner / Dimensiones embalaje / Abmessungen Inner	-
Peso lordo inner / Inner gross weight / Poids brut de l'inner / Peso embalaje / Bruttogewicht Inner	-
Dimensioni display / Display dimensions / Dimensions du présentoir / Dimensiones display/ Abmessungen Display	
Peso lordo display / Display gross weight / Poids brut du présentoir //Peso display - expositor / Bruttogewicht Display	
Dimensioni Master / Master gross dimensions / Dimensions du master / Dimensiones caja master / Abmessungen Master	
Peso lordo master / Master gross weight / Poids brut du master / Peso caja master / Bruttogewicht Master	
Quanti master su un layer 80x120 / How many master cartons per 80x120 cm layers? / Combien de masters par couches 80x120cm? / Cuantas cajas master por capa tamaño 80x120 / Master Kartons pro 80 x 120 cm Fläche / Schicht	
Quanti layer per pallet / How many layers per pallet? / Combien de couches par palettes? / Cuantas capas por paleta / Wie viele Schichten pro Palette? /	
Quanti master su pallet 80x120 / How many master cartons per euro pallet? / Combien de master cartons par euro palettes? // Cuantas cajas master sobre paleta tamaño 80x120 / Wieviele Master Kartons pro Euro-Palette?	

VELAMP IS747-3

 Questo dispositivo è munito di lampade a LED integrate.

A++

A+

A

~~B~~

~~C~~

~~D~~

~~E~~

}

L

E

D

Le lampade di questo dispositivo non sono sostituibili.

874/2012 