





# Data Sheet



- material
1. Body: Nylon-66 (94V-2)
  2. Cover: PC paint mine carving



Rating	Input: 12V/24 DC Output: 5V DC 2.1A+2.1A	Mounting Hole		
Insulation Resistance	DC 500V 100M $\Omega$ Min.			
Dielectric Strength	AC 1500V 1 minute	Thickness(mm)	X(mm)	Y(mm)
Operating Temperature	-0 $^{\circ}$ ~40 $^{\circ}$ C	0.75-1.25	21.0 $^{+0.2}$	36.6 $^{+0.1}$
		1.25-2.0		36.8 $^{+0.1}$
		2.0-3.0		37.0 $^{+0.1}$