

### Safety Instructions

1, 2, 3, 4, 5, 6, 7, 10, 12, 13, 14, 15, 16,  
17, 18, 19, 20, 21, 22, 24, 28, 33, 34



Info

[www.paulmann.com](http://www.paulmann.com)


Paulmann Licht GmbH  
Quezinger Feld 2  
31832 Springe  
Germany

[www.paulmann.com](http://www.paulmann.com)


Art.-Nr.: 942.92  
942.93  
942.94  
942.95  
942.96  
942.97  
942.98  
942.99  
943.00  
943.01  
943.02  
943.03  
943.04  
943.05  
943.06



942.92\_942.94\_942.96



1x




1x



2x


943.06




1x



942.93\_942.95\_942.97



3x




3x




6x




2x



942.98\_943.00  
943.02\_943.04



1x




1x




2x

942.99\_943.01  
943.03\_943.05



3x




3x




6x




(+MA326) PSPU 01/20



942.92\_942.93  
942.94\_942.95  
942.96\_942.97



942.98\_942.99  
943.00\_943.01  
943.02\_943.03  
943.04\_943.05




**A**

**Safety Instructions**  
 Nr. 1, 4, 5, 7 off

item number	hole size
942.92_942.93 942.94_942.95	ø54mm
942.96_942.97	ø55mm
942.98_942.99 943.00_943.01 943.02_943.03 943.04_943.05	ø54mm

ø x mm




**C**

a.

b.


**Safety Instructions**  
 Nr. 3, 4, 5, 6

230V~



**E**

230V~



230V~

OK

15°

230V~

942.92\_942.93  
942.94\_942.95  
942.96\_942.97

230V~

942.98\_942.99  
943.00\_943.01  
943.02\_943.03  
943.04\_943.05

**ENERGY LABEL**

Y IJA  
IE IA

енергия · ενεργεια

A++  
A+  
**A+**  
A  
B  
C  
D  
E

4 kWh/1000h

ø35 mm

**300 lm**  
4 W  
230 V

warm white  
2700K

CRI/Ra ≥ 80

ON OFF >50.000

Lumen 60% <1 s

≈30x  
1.000h

CE

PAP

390094306