

# TOSHIBA



**65UL6B63DG**

**UL6B Series**

**UL6B Series | EAN: 5055862329719**

- ④ 4K HDR UHD
- ④ TRU Picture Engine
- ④ 4x HDMI, 2x USB
- ④ Dolby Vision HDR
- ④ Sound by Onkyo
- ④ Dolby Atmos

CONNECT TV SECURE SMART TV prime video NETFLIX

**A+**

172kWh

118W

<0.5W

# TOSHIBA

## 65UL6B63DG

Größe (cm & Zoll)

65" / 164cm

Auflösung

Ultra HD (3840 x 2160)

Paneltyp

Direct Back Light (DLED)

Prozessortyp

Quad Core

Total Picture Quality

2200

 CONNECT TV

 SECURE  
SMART TV

prime video  


NETFLIX

 HDR 10

 T R U  
MICRO DIMMING

 T R U  
F L O W

 T R U  
RESOLUTION

SOUND BY  
ONKYO

 DOLBY VISION™

## BILDSCHIRM

Größe (cm & Zoll)	65" / 164cm
Auflösung	Ultra HD (3840 x 2160)
Paneltyp	Direct Back Light (DLED)
Helligkeit	350

## VIDEO

HDR	Ja
Dolby Vision HDR	Ja
MEMC	Ja
UHD-UpScaler	Ja
Bildmodi	Dynamic, Game, Sports, Cinema, Natural, Dolby Vision Bright, Dolby Vision Dark, User

## TON

Sound by Onkyo	Ja
Audio-Ausgangsleistung (RMS)	2x12W
Dolby Audio™	Ja
DTS™ Decoder	Ja
Interner Subwoofer	Ja
Lautsprechertyp	Abfeuern
Equalizer	5 band
Ger (D) + Nicam Stereo	Ja
Sound-Modusarten	Musik, Film, Sprache, Klassik, Flat, Benutzer

## LEISTUNGS-AUFNAHME / ENERGIE

Energieeffizienzklasse (ErP Rang)	A+
Energieverbrauch im Standby (Durchschnitt)	<0.5W
Energieverbrauch (Watt) (Durchschnitt)	118W
Jahresenergieverbrauch (Durchschnitt)	172kWh
Betriebsspannung – Frequenz	220-240V AC
Blei (mg)	0
Quecksilber (mg)	0
12V TV (Mobile TV)	Nein

## HAUPTFUNKTIONEN

Smart TV	Ja
Prozessorotyp	Quad Core
TV-DVD-Kombination	Nein
Total Picture Quality	2200

## TUNER / TV-ÜBERTRAGUNG

Tunertyp	HD DVB-T2/C/S2
Dualer Tuner	No
UHD über Satellit	Ja
HEVC-Dekodierer (H.265)	Ja
Hybrid Log Gamma (HLG)	Ja
Freesat	No
EPG (Elektronischer Programmführer)	Ja
Automatische Suche	Ja
Programmspeicherkapazität (Analog)	200
Programmspeicherkapazität (Digital S/S2)	10000
Programmspeicherkapazität (Digital T/T2/C)	800

## SMART-TV-FUNKTIONEN

Toshiba Smart Portal	Ja
HBB TV ver 1.5	Ja
Webbrowser	Ja
Netflix®	Ja
Prime Video	Ja
Netflix® 4K	Ja
YouTube™	Ja
YouTube™ 4K	Ja
Integriertes WLAN	Internal
Bluetooth®	Ja
FollowMe TV	Ja
Audio-Video Sharing (AVS)	Ja
Bildschirm Spiegelung (Miracast)	Ja
Smart Guide-Anwendung	Ja
Smart Remote-Anwendung	Ja
Amazon Works with Alexa	Built in Alexa

## MECHANISCH

Abmessungen mit Verpackung (mm)	1620 x 165 x 1010
Abmessungen ohne Verpackung (mm)	1456 x 251 x 875
Abmessungen ohne Ständer (mm)	1456 x 72 x 840
Bruttogewicht (kg)	0
Eigengewicht (kg)	0
VESA (Wandhalterung) BxH	400mm x 200mm

## ANSCHLÜSSE

Antenneneingang	Ja
HDMI™	4 HDMI
USB	2 USB
Scart	No
VGA (PC in - D-Sub15)	Ja
CI+	Ja
Komponente (YPbPr) in	via VGA
Kompositvideo/Audio in	Ja
Digitaler Audioausgang	Optik
Ethernet	Ja
Kopfhörer ausgehend	Ja

## FUNKTIONEN

Mediaplayer	Ja
USB-Aufzeichnung (PVR Ready)	Nein
Multimedia-Anwendungen	Video:.mpg, .mpeg, .dat, .vob, .mkv, .mp4, .mov, .flv, .3gp, .avi; Audio:.mp3, .wma, .wav; Picture:.jpg, .jpeg, .bmp, .png
Kanallisten USB-Cloning	Ja
HDMI™ ARC	Über HDMI2
HDMI™ CEC	Ja
MHL via HDMI® (Mobil-HD-Link)	Nein
Teletext	Ja
Kindersicherung	Ja
NTSC-Wiedergabe	Ja
Einfacher Hotel-Modus	Passiv-grundlegender Hotelmodus

"Toshiba" is a registered trademark of Toshiba Corporation and its used by Vestel or its subsidiary for products described here in under license from Toshiba Visual Solutions Corporation. All other product and brand names are trademarks or registered trademarks of their respective companies. Design, features and specifications are subject to change without notice. Non-metric weights and measurements are approximate. Screen images are simulated.