



|                               |   |
|-------------------------------|---|
| Part No                       | 90NB0Q92-M01750   |
| Model Name                    | F409JA-EK048T   |
| EAN Code                      | 4718017860901   |
| UPC Code                      | 192876860908  |
| Operating System              | Windows 10 Home - ASUS recommends Windows 10 Pro for business               |
| Office                        | 1-month trial for new Microsoft 365 customers. Credit card required.        |
| LCD cover-material            | Plastic   |
| LCD cover-color               | Slate Grey  |
| Top case-material             | Plastic   |
| Top case-color                | Slate Grey  |
| Bottom case-material          | Plastic   |
| Bottom case-color             | Slate Grey  |
| Military grade                | N/A   |
| Panel Size                    | 14.0-inch   |
| Backlit                       | LED Backlit   |
| Brightness                    | 220nits   |
| Resolution                    | FHD (1920 x 1080) 16:9  |
| Glare                         | Anti-glare display  |
| Color gamut                   | NTSC: 45%   |
| Touch Panel                   | N/A   |
| Screen-to-body ratio          | 78%   |
| Pantone                       | N/A   |
| IPS-level                     | N/A   |
| Processor                     | Intel® Core™ i3-1005G1 Processor 1.2 GHz (4M Cache, up to 3.4 GHz, 2 cores) |
| Chipset                       | N/A   |
| Discrete/Share                | Share   |
| Intergrated GPU               | Intel® HD Graphics 520  |
| VRAM                          | N/A   |
| Expansion Slot(includes used) | 1x DDR4 SO-DIMM slot<br>1x M.2 2280 PCIe 3.0x2<br>1x STD 2.5" SATA HDD      |
| Total System Memory           | 4GB DDR4 on board + 4GB DDR4 SO-DIMM  |
| On board memory               | 4GB DDR4 on board   |
| DIMM Memory                   | 4GB DDR4 SO-DIMM  |
| Storage                       | 256GB M.2 NVMe™ PCIe® 3.0 SSD   |
| Front-facing camera           | N/A   |
| Rear-facing camera            | VGA camera//Without privacy shutter   |
| World-facing camera           | N/A   |

|                                 |   |
|---------------------------------|---|
| Wireless                        | Wi-Fi 5(802.11ac)+Bluetooth 4.1 (Dual band) 1*1   |
| 3G/4G                           | N/A   |
| NumberPad                       | N/A   |
| ScreenPad™                      | N/A   |
| FingerPrint                     | N/A   |
| I/O ports                       | 1x 3.5mm Combo Audio Jack<br>1x HDMI 1.4//2x USB 2.0 Type-A<br>1x USB 3.2 Gen 1 Type-A<br>1x USB 3.2 Gen 1 Type-C//Micro SD card reader     |
| Audio                           | Built-in speaker<br>Built-in microphone<br>SonicMaster  |
| Voice control                   | with Cortana support  |
| AC Adapter                      | ø4.0, 45W AC Adapter, Output: 19V DC, 2.37A, 45W, Input: 100~240V AC 50/60Hz universal  |
| Battery                         | 32WHrs, 2S1P, 2-cell Li-ion   |
| Replaceable Battery             | No  |
| Keyboard type                   | Chiclet Keyboard  |
| Dimension (WxHxD)               | 32.50 x 21.60 x 2.31 ~ 2.31 cm  |
| Weight (with Battery)           | 1.60 kg   |
| Weight (without Battery)        | 1.40 kg   |
| Security                        | Security Lock<br>Trusted Platform Module (Firmware TPM)   |
| MyASUS feature                  | Link to MyASUS (All models, Bluetooth needed)<br>Splendid (All models)<br>Tru2Life (Intel Platform models)<br>Keyboard hotkeys (All models) |
| Built-in Apps                   | MyASUS (for all)  |
| Included in the Box             | N/A   |
| Reparability Index (for France) | 6.6   |