

KERN 346-77

KERN

Individual weight, OIML Class M1, 10 kg, Block Eco, cast iron lacquered



Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	210×110×125 mm
Shipping method	Parcel service
Net weight approx.	10 kg
Gross weight approx.	10 kg
Shipping weight	10 kg

Optional cases

Case - Aluminium article number	346-070-600
---------------------------------	-------------

Product information

GTIN/EAN number	4045761241688
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



Category

Brand	KERN
Product category	Individual weight
Product group	OIML M1
Product family	346

Measuring System

Test weight - volume (cm ³)	1408,4507
Conformity assessment possible	✓
Test weight - Density uncertainty (kg/m ³)	600
Test weight - volume uncertainty (cm ³)	119,024
Weight OIML class	M1
Test weight - nominal value	10 kg
Permissible tolerance according to OIML (+/-)	500 mg
Test weight - Density (kg/m ³)	7100
OIML-compliant	✓
Test weight - Density [Min] (OIML)	3000

Construction

Shape weight	Block Eco
Dimensions weight (W×D×H)	190×93×110 mm
Material	cast iron lacquered
Adjustment method	Adjusting cavity - Seal

Services (optional)

Article number for DAkkS calibration	962-644
--------------------------------------	---------