

2USB inCharge PRO SI 15W

General Information

Name	inCharge PRO SI EU F
SKU	2U-449368 (Glossy White) 2U-449382 (Glossy Cream)

Basics

Brand	2USB
Model Number	5503FBCX
EAN	8718868449368 (Glossy White) 8718868449382 (Glossy Cream)
Customs Number (HS-Code)	8536.69.90.99

Dimensions

Depth in mm	45
Height in mm	71
Width in mm	71
Nett Weight in gram	92
Gross Weight in gram	130
Mounting Depth in mm	32

Technical Specifications

Output Voltage	4,75 - 5,25VDC
Energy Efficiency in %	82%
Stand-by Power Loss in mW	<80mW
Socket Type	CEE Type 7/3 (F)
Power Rating	16A / 3680W
Terminal Type	Double, with Clamps
Stripping Length in mm	11
Expected lifetime in hours at Full Load	20000
Overvoltage Category	III
Operating Temperature	0-40°C
Output Current	0,01 - 3,0A (shared)
Wiring	1,5 mm ² - 2*2,5mm ² rigid, stranded or flexible
Input Voltage	250V~50Hz
Input Current	Max. 500mA
Storage Temperature	-20°C - 80°C

Standards & Certifications

Certifications	CE, KEMA-KEUR, VDE
EU Directives	RoHS Directive (2011/65/EU), EMC Directive (2014/30/EU), Low Voltage Directive (2014/35/EU), ErP Directive (2009/125/EC)
Socket Outlet Standards	NEK 502:2016, NEN 1020:1987+A2:2004, DIN VDE0620-1:2016, SFS 5610:2004:+A1:2008, UNE 20315-1-1:2009, SS 428 08 34:2013, NP 1620:1993 (Ed.2), UNE 20135-2-7:2008, IEC 60884-1:2010, ÖNORM E 8684-1:2010
EMC & LVD Standards	EN 60669-2-1 (clause 26), EN 55032 (class B), EN 55024, IEC-EN 61558-2-16, IEC-EN 62368-1, IEC-EN 61558-1