

# DIR-250BK

Internet, DAB+, FM Tuner  
with Bluetooth and Spotify Connect

More than  
**30,000**  
Radio Stations  
from All Over  
the World



APP CONTROL



### EN

- Internet radio for receiving radio stations from all over the world
- WiFi and ethernet connections
- DAB+
- PLL FM radio
- Spotify connect
- Bluetooth 5.0
- 3.2" (8,1cm) TFT LCD color display
- Multiple OSD languages
- Audio formats : MP3, WAV, AAC
- DLNA and UPnP
- Connections: 3.5mm earphone jack, Optical output, Coaxial output, RCA output, 75 Ohm, RJ45
- Included : Remote control, AC Adaptor, 2 antennas

### DE

- Internet Radio für Radiosender aus aller Welt
- WiFi und Ethernet Verbindungen
- DAB+
- PLL FM Radio
- Spotify connect
- Bluetooth 5.0
- 3,2" (8,1 cm) TFT LCD-Bildschirm
- Mehrere OSD-Sprachen
- Audioformate : MP3, WAV, AAC
- DLNA und UPnP
- Anschlüsse: 3,5 mm Kopfhörerbuchse, Optical-Ausgang, Coaxial-Ausgang, RCA-Ausgang, 75 Ohm, RJ45
- Inklusiv : Fernbedienung, Netzadapter, 2 antennen

### NL

- Internet radio voor ontvangst van radio zenders van de hele wereld
- WiFi en ethernet verbindingen
- DAB+
- PLL FM radio
- Spotify connect
- Bluetooth 5.0
- 3,2" TFT LCD kleurenscherm (8,1 cm)
- Meerdere OSD talen
- Ondersteunde audio formaten : MP3, WAV, AAC
- DLNA en UPnP
- Aansluitingen: 3,5 mm hoofdtelefoon uitgang, Optische uitgang, Coaxiale uitgang, RCA uitgang, 75 Ohm, RJ45
- Inclusief: Afstandsbediening, AC-adapter, 2 antennes

### FR

- Radio internet pour la réception de stations de radio du monde entier
- Connexions WiFi et ethernet
- DAB+
- Radio FM avec tuner PLL
- Spotify connect
- Bluetooth 5.0
- Écran couleur TFT LCD de 3,2" (8,1 cm)
- Affichage multi-langues
- Formats audio supportés : MP3, WAV, AAC
- DLNA et UPnP
- Connexions: Prise casque 3,5 mm, Sortie Optique, Sortie Coaxiale, Sortie RCA, 75 Ohm, RJ45
- Inklus: Commande à distance, Adaptateur secteur, 2 antennes

### ES

- Radio por Internet para recibir emisoras de radio de todo el mundo
- WiFi y ethernet conexiones
- DAB+
- Radio FM PLL
- Spotify connect
- Bluetooth 5.0
- Pantalla TFT LCD de 3,2" (8,1 cm)
- Idiomas multiples OSD
- Formatos audio : MP3, WAV, AAC
- DLNP y UPnP
- Conexiones : jack para auriculares de 3.5mm, Salida Optical, Salida Coaxial, Salida RCA, 75 Ohm, RJ45
- Incluye : Mando a distancia, Adaptador CA, 2 antenas

### DATA

- Power source: AC 100-240V~50/60 Hz
- Power consumption max: 7,5W
- Dim. unit : 430 x 287 x 72 mm (WxDxH)
- Gift box Dim. : 516 x 368 x 132 mm (WxDxH)
- Net/Gross Weight: 2.2 kgs / 3,4 kgs
- Master carton quantity: 2pcs
- EAN-code : 871 1902044215
- Custom code : 8527910000
- Container quantity :  
20'ft : 1000 pcs  
40'ft : 2070 pcs  
40'HQ : 2425 pcs

Subject to changes without prior notice

