

PowerPlay²⁰

Perfection in every detail. We took all the best from the PowerPlay¹⁰ and doubled its capacity!
With our Green Cell PowerPlay²⁰ power bank, you can extend the life of your devices by several hours!

DESIGN

PowerPlay²⁰ was designed to be similar to our previous power banks as we wanted to keep this distinctive look. Its high-quality lithium-polymer cells are protected by an elegant and extremely durable housing. PowerPlay²⁰ fits perfectly with the latest smartphones and attracts attention.

CHARGING PORTS

Supply up to three devices at the same time with fresh energy! Two USB ports supporting Ultra Charge technology (up to 3.5x faster charging compared to standard chargers!) and a USB-C standard Power Delivery 18 W port, which you can also connect to a console or a tablet. PowerPlay²⁰ can be charged with an additional USB-C port.

BE UNRIVALED

Because of high-quality lithium-polymer cells GC PowerPlay²⁰ will ensure maximum working time for your devices, extending it by several hours! That is what makes it a great travel companion – you can take it anywhere you go!

+72h

iPhone
11 / XS / X

+64h

Xiaomi
Mi Mix 3 / Mi 9

+56h

Samsung
S10 / S10e

+44h

Huawei
P30 Pro

+20h

iPad PRO

+12h

Nintendo
Switch

TECHNICAL SPECIFICATION

Capacity: **20000 mAh**

Type of cells: **Li-Polymer**

USB-C1 input: **5V/2A, 9V/2A Max 18 W**

USB-C2 input: **5V/2A, 9V/2A Max 18 W**

USB-C2 output: **5V/2,4A 9V/2A 12V/1.5A Max 18 W**

2x USB-A: **5V/2,4A 9V/2A 12V/1.5A Max 18 W**

Compatible quick-charging technologies:

GC Ultra Charge, Quick Charge 3.0, Samsung AFC, Huawei FCP, Apple 2.4A, Mediatek Pump Express

1.1/2.0, USB DCP, Power Delivery

Pass-Through: **Yes**

Dimensions: **140x73x25 mm**

Weight: **341 g**

Set includes: **GCmatte 25 cm USB-C**

Overheating protection: **YES**

Deep discharge protection: **YES**

Overload protection: **YES**

