

Crimping pliers - CRIMPFOX CENTRUS 6S-NC - 1202882

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimping tool, for uninsulated and insulated ferrules, DIN 46228 Part 1 and 4, from 0.14 mm² ... 6 mm², also for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, lateral insertion

Your advantages

- ✓ Ergonomic handle design ensures comfortable, fatigue-free handling
- ✓ With a particularly small handle width, the tool fits perfectly in your hand
- ✓ Clear view into the crimping area
- ✓ Up to 30% lower actuation force, thanks to optimized leverage
- ✓ Pressure lock ensures consistently high quality crimping results



Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 267377
GTIN	4063151267377
Weight per Piece (excluding packing)	368.740 g
Weight per piece (including packing)	453.200 g
Custom tariff number	82032000
Country of origin	Sweden
Sales Key	N2 - Printer Asses.+ Tool
Note	Made to Order (non-returnable)

Technical data

Dimensions

Length (b)	175 mm
Width (a)	65 mm
Height (c)	22 mm

General

Note	DIN 46228-1, DIN 46228-4
------	--------------------------

Crimping pliers - CRIMPFOX CENTRUS 6S-NC - 1202882

Technical data

General

Color	black/green
Compression	Square crimp
Type of contact	Insulated and uninsulated ferrules
Min. cross section	0.14 mm ²
Max. cross section	6 mm ²
AWG min	26
AWG max	10

Classifications

eCl@ss

eCl@ss 9.0	21043811
------------	----------

Accessories

Accessories

Mounting material

Replacement spring - CRIMPFOX/ SPR-4 - 1200288



Spare recuperating spring

Replacement handle - CRIMPFOX CENTRUS NC/U-HANDLE - 1202880



Replacement upper handle for CRIMPFOX CENTRUS series