

Thermal transfer printer - THERMOMARK GO - 1090747

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Mobile thermal transfer printer for marking materials in cartridge format incl. accessories. The printer can print pre-punched labels as well as materials in continuous format up to a material width of 24 mm. Scope of supply: battery, power supply unit incl. 4 adapters, USB cable, MM-EML (20X8)R C1 WH/BK, quick guide

Product Description

The THERMOMARK GO is a mobile printer which elevates the digitalization of industrial identification to a new level with its intuitive operation via smart device. Controlled via the MARKING system app, the robust printer creates markings directly on site. Features such as state-of-the-art interfaces, fully guided creation of application-specific marking solutions, and automatic material detection make the process of creating markings particularly easy and error-free. The ability to print punched materials as well as continuous media offers professional users a wide variety of applications in industry and trade.

Note:

This product is approved for the following countries only and may only be used in these countries.

Andorra, Austria, Belgium, Bulgaria, Canada, China, Croatia, Cyprus, Czech Republic, Denmark, Estonia, Finland, France, Germany, Greece, Hungary, Iceland, Ireland, Italy, Latvia, Liechtenstein, Lithuania, Luxembourg, Malta, Netherlands, Norway, Poland, Portugal, Romania, Russia, San Marino, Slovakia, Slovenia, Spain, Sweden, Switzerland, Turkey, USA

Your advantages

- ✓ Maintenance-free operation with proven thermal transfer printing technology
- ✓ Printing of pre-punched die-cut materials and continuous media; adhesive labels, marking labels, and shrink sleeve
- ✓ Operated entirely via digital devices using the MARKING system app
- ✓ Alternative control via the PROJECT complete software
- ✓ User-friendly operation with context-based menu navigation of the MARKING system app and Application Wizards for easily creating application-specific marking solutions
- ✓ The THERMOMARK GO prints materials in cartridge format, which contain the material to be marked and the appropriate ink ribbon
- ✓ Easy material change with the uniform GO SERIES cartridge system



Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 901510
GTIN	4055626901510
Weight per Piece (excluding packing)	743.000 g
Weight per piece (including packing)	1,719.000 g

Thermal transfer printer - THERMOMARK GO - 1090747

Custom tariff number	84433210
Country of origin	China
Sales Key	N1 - Printer+autom.Tools

Technical data

General

Interface	USB
	Bluetooth
Weight	743 g

Dimensions

Length	70 mm
Height	175 mm
Width	135 mm

Connection data

Minimum voltage	100 V AC
Max. voltage	240 V AC
Additional text	50 Hz ... 60 Hz

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 10;
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 9.0	19140104
------------	----------

Approvals

Approvals

Approvals

FCC / Industry Canada / cULus Listed / EAC-RoHS / CCC / EAC / EAC

Ex Approvals

Approval details

FCC	SQBL652
-----	---------

Industry Canada	3147A-BL652
-----------------	-------------

Thermal transfer printer - THERMOMARK GO - 1090747

Approvals

cULus Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E140403
EAC-RoHS			RU D- DE.HB49.B.00023
CCC			2020010904307912
EAC			RU D- DE.GB09.B.00141
EAC			RU0000049188

Accessories

Accessories

Conductor marking

Cable marker label - MM-WML 3 (EX10)R C1 WH/BK - 0803931



Cable marker label, Roll, white, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K:
without print, mounting type: adhesive, lettering field size: continuous x 10 mm

Cable marker label - MM-WML 5 (EX10)R C1 WH/BK - 0803932



Cable marker label, Roll, white, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K:
without print, mounting type: adhesive, lettering field size: continuous x 10 mm

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Cable marker label - MM-WML 3 (EX10)R C1 YE/BK - 1116137



Cable marker label, Roll, yellow/black, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX: without print, mounting type: adhesive, lettering field size: continuous x 8 mm

Cable marker label - MM-WML 5 (EX10)R C1 YE/BK - 1116138



Cable marker label, Roll, yellow/black, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX: without print, mounting type: adhesive, lettering field size: continuous x 8 mm

Shrink sleeve - MM-WMS 6,4 (EX10)R C1 YE/BK - 1116141



Shrink sleeve, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: slide-on, cable diameter range: 2.1 ... 6.4 mm, lettering field size: continuous x 8.2 mm

Shrink sleeve - MM-WMS 9,5 (EX16)R C1 YE/BK - 1116142



Shrink sleeve, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: slide-on, cable diameter range: 3.2 ... 9.5 mm, lettering field size: continuous x 12.8 mm

Shrink sleeve - MM-WMS-2 3,2 (EX5)R C1 YE/BK - 1116176



Shrink sleeve, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOFOX, mounting type: slide-on, cable diameter range: 1.6 ... 3.2 mm, lettering field size: continuous x 3.7 mm

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Shrink sleeve - MM-WMS-2 4,8 (EX9)R C1 YE/BK - 1116186



Shrink sleeve, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOFOX, mounting type: slide-on, cable diameter range: 2.4 ... 4.8 mm, lettering field size: continuous x 6.1 mm

Shrink sleeve - MM-WMS-2 6,4 (EX10)R C1 YE/BK - 1116187



Shrink sleeve, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOFOX, mounting type: slide-on, cable diameter range: 3.2 ... 6.4 mm, lettering field size: continuous x 8.5 mm

Shrink sleeve - MM-WMS-2 9,5 (EX16)R C1 YE/BK - 1116189



Shrink sleeve, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOFOX, mounting type: slide-on, cable diameter range: 4.8 ... 9.5 mm, lettering field size: continuous x 12.5 mm

Label - MM-EML (15X6)R C1 YE/BK - 1116160



Label, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: adhesive, lettering field size: 15 x 6 mm, Number of individual labels: 321

Cable marker - MM-WML 14 (24X19)R C1 WH/BK - 1116146



Cable marker, Roll, white/black, can be labeled with: THERMOMARK GO: without print, mounting type: adhesive, lettering field size: 22 x 19 mm, Number of individual labels: 93

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Cable marker - MM-WML 5 (24X10)R C1 WH/BK - 1116196



Cable marker, Roll, white/black, unlabeled, can be labeled with: THERMOMARK GO: without print, mounting type: adhesive, lettering field size: 22 x 9.5 mm, Number of individual labels: 235

Cable marker - MM-WML 6 (13X13)R C1 WH/BK - 1116197



Cable marker, Roll, white/black, can be labeled with: THERMOMARK GO: without print, mounting type: adhesive, lettering field size: 12.7 mm x 12.7 mm, Number of individual labels: 190

Cable marker - MM-WML 7,5 (24X13)R C1 WH/BK - 1116198



Cable marker, Roll, white/black, can be labeled with: THERMOMARK GO: without print, mounting type: adhesive, lettering field size: 22 x 12.7 mm, Number of individual labels: 165

Cable marking flags - MM-WML-FLAG 6 (20X10)R C1 WH/BK - 1116143



Cable marking flags, Roll, white/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: adhesive, lettering field size: 20 x 10 mm, Number of individual labels: 145

Cable marking flags - MM-WML-FLAGV 6 (20X10)R C1 WH/BK - 1116190



Cable marking flags, Roll, white/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: adhesive, lettering field size: 20 x 10 mm, Number of individual labels: 145

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Cable marker - MM-WMT 2,4 (15X4)R C1 WH/BK - 1116144



Cable marker, Roll, white, unlabeled, can be labeled with: THERMOMARK GO, mounting type: insert, cable diameter range: 1 ... 2.4 mm, lettering field size: 14.1 mm x 3.2 mm, Number of individual labels: 354

Cable marker - MM-WMT 3,5 (15X5)R C1 WH/BK - 1116191



Cable marker, Roll, white, unlabeled, can be labeled with: THERMOMARK GO, mounting type: insert, cable diameter range: 2 ... 3.5 mm, lettering field size: 14.2 mm x 4 mm, Number of individual labels: 338

Cable marker - MM-WMT 4,2 (15X6)R C1 WH/BK - 1116192



Cable marker, Roll, white, unlabeled, can be labeled with: THERMOMARK GO, mounting type: insert, cable diameter range: 3 ... 4.2 mm, lettering field size: 14.2 mm x 5 mm, Number of individual labels: 324

Cable marker - MM-WMT 5,5 (15X8)R C1 WH/BK - 1116193



Cable marker, Roll, white, unlabeled, can be labeled with: THERMOMARK GO, mounting type: insert, cable diameter range: 4 ... 5.5 mm, lettering field size: 14 mm x 7 mm, Number of individual labels: 320

Cable marker - MM-WMT 8,4 (17X10)R C1 WH/BK - 1116194



Cable marker, Roll, white, unlabeled, can be labeled with: THERMOMARK GO, mounting type: insert, cable diameter range: 5 ... 8.4 mm, lettering field size: 16 mm x 7.4 mm, Number of individual labels: 260

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Cable marker - MM-WMTB (24X8)R C1 WH/BK - 1116145



Cable marker, Roll, white/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: Assembly with cable binders, lettering field size: 20 mm x 7 mm, Number of individual labels: 186

Cable marker - MM-WMTB HF (40X12)R C1 WH/BK - 1116166



Cable marker, Roll, white/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: Assembly with cable binders, lettering field size: 40 mm x 8.5 mm, Number of individual labels: 50

Cable marker - MM-WMTB HF (40X12)R C1 YE/BK - 1116206



Cable marker, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: Assembly with cable binders, lettering field size: 40 mm x 8.5 mm, Number of individual labels: 50

Cable marker - MM-WMTB HF (55X15)R C1 WH/BK - 1116207



Cable marker, Roll, white/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: Assembly with cable binders, lettering field size: 55 mm x 13.4 mm, Number of individual labels: 20

Cable marker - MM-WMTB HF (55X15)R C1 YE/BK - 1116208



Cable marker, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: Assembly with cable binders, lettering field size: 55 mm x 13.4 mm, Number of individual labels: 20

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Cable marker - MM-WMTB HF (55X25)R C1 WH/BK - 1116209



Cable marker, Roll, white/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: Assembly with cable binders, lettering field size: 55 mm x 22 mm, Number of individual labels: 20

Cable marker - MM-WMTB HF (55X25)R C1 YE/BK - 1116210



Cable marker, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: Assembly with cable binders, lettering field size: 55 mm x 22 mm, Number of individual labels: 20

Device marking

Label - MM-EML (EX10)R C1 SR/BK - 0803974



Label, Roll, silver, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Label - MM-EML (EX10)R C1 WH/BK - 0803970



Label, Roll, white/black, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Label - MM-EML (EX12)R C1 SR/BK - 0803975



Label, Roll, silver, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Label - MM-EML (EX12)R C1 WH/BK - 0803971



Label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K,
mounting type: adhesive, lettering field size: continuous x 12 mm

Label - MM-EML (EX18)R C1 SR/BK - 0803976



Label, Roll, silver, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K,
mounting type: adhesive, lettering field size: continuous x 18 mm

Label - MM-EML (EX18)R C1 WH/BK - 0803972



Label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K,
mounting type: adhesive, lettering field size: continuous x 18 mm

Label - MM-EML (EX24)R C1 SR/BK - 0803978



Label, Roll, silver, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K,
mounting type: adhesive, lettering field size: continuous x 24 mm

Label - MM-EML (EX24)R C1 WH/BK - 0803973



Label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K,
mounting type: adhesive, lettering field size: continuous x 24 mm

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Fabric label - MM-EMLC (EX10)R C1 WH/BK - 0803933



Fabric label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Fabric label - MM-EMLC (EX12)R C1 WH/BK - 0803934



Fabric label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Fabric label - MM-EMLC (EX18)R C1 WH/BK - 0803936



Fabric label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Label, highly flexible - MM-EMLF (EX10)R C1 BU/WH - 0803945



Label, highly flexible, Roll, blue, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Label, highly flexible - MM-EMLF (EX10)R C1 GN/WH - 0803950



Label, highly flexible, Roll, green, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Label, highly flexible - MM-EMLF (EX10)R C1 OG/BK - 0803955



Label, highly flexible, Roll, orange, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Label, highly flexible - MM-EMLF (EX10)R C1 RD/WH - 0803959



Label, highly flexible, Roll, red, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Label, highly flexible - MM-EMLF (EX10)R C1 WH/BK - 0803937



Label, highly flexible, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Label, highly flexible - MM-EMLF (EX10)R C1 YE/BK - 0803941



Label, highly flexible, Roll, yellow, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Label, highly flexible - MM-EMLF (EX12)R C1 BU/WH - 0803946



Label, highly flexible, Roll, blue, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Label, highly flexible - MM-EMLF (EX12)R C1 GN/WH - 0803952



Label, highly flexible, Roll, green, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Label, highly flexible - MM-EMLF (EX12)R C1 OG/BK - 0803956



Label, highly flexible, Roll, orange, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Label, highly flexible - MM-EMLF (EX12)R C1 RD/WH - 0803960



Label, highly flexible, Roll, red, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Label, highly flexible - MM-EMLF (EX12)R C1 WH/BK - 0803938



Label, highly flexible, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Label, highly flexible - MM-EMLF (EX12)R C1 YE/BK - 0803942



Label, highly flexible, Roll, yellow, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Label, highly flexible - MM-EMLF (EX18)R C1 BU/WH - 0803947



Label, highly flexible, Roll, blue, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Label, highly flexible - MM-EMLF (EX18)R C1 GN/WH - 0803953



Label, highly flexible, Roll, green, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Label, highly flexible - MM-EMLF (EX18)R C1 OG/BK - 0803957



Label, highly flexible, Roll, orange, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Label, highly flexible - MM-EMLF (EX18)R C1 RD/WH - 0803961



Label, highly flexible, Roll, red, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Label, highly flexible - MM-EMLF (EX18)R C1 WH/BK - 0803939



Label, highly flexible, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Label, highly flexible - MM-EMLF (EX18)R C1 YE/BK - 0803943



Label, highly flexible, Roll, yellow, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Label, highly flexible - MM-EMLF (EX24)R C1 BU/WH - 0803949



Label, highly flexible, Roll, blue, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 24 mm

Label, highly flexible - MM-EMLF (EX24)R C1 GN/WH - 0803954



Label, highly flexible, Roll, green, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 24 mm

Label, highly flexible - MM-EMLF (EX24)R C1 OG/BK - 0803958



Label, highly flexible, Roll, orange, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 24 mm

Label, highly flexible - MM-EMLF (EX24)R C1 RD/WH - 0803962



Label, highly flexible, Roll, red, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 24 mm

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Label, highly flexible - MM-EMLF (EX24)R C1 WH/BK - 0803940



Label, highly flexible, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 24 mm

Label, highly flexible - MM-EMLF (EX24)R C1 YE/BK - 0803944



Label, highly flexible, Roll, yellow, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 24 mm

Insert label - MM-EMT (EX15)R C1 WH/BK - 0803966



Insert label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snapped into marker carrier, lettering field size: continuous x 15 mm

Insert label - MM-EMT (EX17)R C1 WH/BK - 0803967



Insert label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snapped into marker carrier, lettering field size: continuous x 17 mm

Insert label - MM-EMT (EX18)R C1 WH/BK - 0803968



Insert label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snapped into marker carrier, lettering field size: continuous x 18 mm

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Insert label - MM-EMT (EX23)R C1 WH/BK - 0803969



Insert label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snapped into marker carrier, lettering field size: continuous x 23 mm

Insert label - MM-EMT (EX6)R C1 WH/BK - 0803963



Insert label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snapped into marker carrier, lettering field size: continuous x 6 mm

Insert label - MM-EMT (EX8)R C1 WH/BK - 0803965



Insert label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snapped into marker carrier, lettering field size: continuous x 8 mm

Insert label - MM-EMT (EX4)R C1 WH/BK - 1169312



Insert label, Roll, white/black, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: insert, lettering field size: continuous x 3 mm

Label - MM-EML (EX8)R C1 YE/BK - 1116050



Label, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 6 mm

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Label - MM-EML (EX10)R C1 YE/BK - 1116052



Label, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 8 mm

Label - MM-EML (EX12)R C1 YE/BK - 1118734



Label, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 10 mm

Label - MM-EML (EX14)R C1 WH/BK - 1116982



Label, Roll, white/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 12 mm

Label - MM-EML (EX14)R C1 TR/BK - 1116981



Label, Roll, transparent/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 12 mm

Label - MM-EML (EX14)R C1 YE/BK - 1116983



Label, Roll, yellow/black, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 12 mm

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Label - MM-EML (EX14)R C1 SR/BK - 1116113



Label, Roll, silver/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 12 mm

Label - MM-EML (EX18)R C1 YE/BK - 1116114



Label, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 16 mm

Label - MM-EML (EX18)R C1 TR/BK - 1116130



Label, Roll, transparent/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 16 mm

Label - MM-EML (EX24)R C1 YE/BK - 1116131



Label, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 22 mm

Label - MM-EML (EX24)R C1 TR/BK - 1116133



Label, Roll, transparent/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 22 mm

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Fabric label - MM-EMLC (EX14)R C1 WH/BK - 1116134



Fabric label, Roll, white/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 12 mm

Label - MM-EMLF (EX14)R C1 WH/BK - 1116135



Label, Roll, white/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 12 mm

Label - MM-EMLF (EX14)R C1 YE/BK - 1116136



Label, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 12 mm

Label - MM-EML (15X9)R C1 YE/BK - 1116199



Label, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: adhesive, lettering field size: 15 x 9 mm, Number of individual labels: 285

Label - MM-EML (16,5X5)R C1 WH/BK - 1116200



Label, Roll, white/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: adhesive, lettering field size: 16.5 x 5 mm, Number of individual labels: 335

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Label - MM-EML (16,5X5)R C1 YE/BK - 1116201



Label, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: adhesive, lettering field size: 16.5 x 6 mm, Number of individual labels: 335

Label - MM-EML (17,5X8)R C1 YE/BK - 1116203



Label, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: adhesive, lettering field size: 17.5 x 8 mm, Number of individual labels: 297

Label - MM-EML (20X8)R C1 WH/BK - 1116204



Label, Roll, white/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: adhesive, lettering field size: 20 mm x 8 mm, Number of individual labels: 297

Label - MM-EML (20X8)R C1 YE/BK - 1116205



Label, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, mounting type: adhesive, lettering field size: 20 mm x 8 mm, Number of individual labels: 297

Printing system accessories

Battery - THERMOFOX/ACCU - 0805009



Battery for mobile operation of the THERMOMARK GO and THERMOMARK GO.K / THERMOFOX printers.

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Power supply unit - THERMOFOX/ADAPTER - 0805010



Power supply unit incl. 4 adapters for operation of the THERMOMARK GO and THERMOMARK GO.K / THERMOFOX printers.

Charging tray - THERMOFOX/CHARGER - 0805012



Charging cradle for charging the THERMOFOX/ACCU battery (0805009), which is required for mobile operation of the THERMOMARK GO and THERMOMARK GO.K / THERMOFOX printers.

Transport bag - THERMOMARK GO BAG - 1229457



Flexible shoulder bag and belt pouch in one for the THERMOMARK GO mobile printer. Additional pockets provide space for a smartphone and materials.

Case - THERMOMARK GO CASE - 1229456



Practical and robust case for storing the THERMOMARK GO and THERMOMARK GO.K mobile printers as well as necessary accessories. The case provides space for nine material cartridges.

Shrink sleeve

Shrink sleeve - MM-WMS 3,2 (EX5)R C1 WH/BK - 0803923



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 1 ... 3.2 mm, lettering field size: continuous x 5 mm

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Shrink sleeve - MM-WMS 4,8 (EX9)R C1 WH/BK - 0803924



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 1.6 ... 4.8 mm, lettering field size: continuous x 9 mm

Shrink sleeve - MM-WMS 6,4 (EX10)R C1 WH/BK - 0803925



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 2.1 ... 6.4 mm, lettering field size: continuous x 10 mm

Shrink sleeve - MM-WMS 9,5 (EX16)R C1 WH/BK - 0803926



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 3.2 ... 9.5 mm, lettering field size: continuous x 16 mm

Shrink sleeve - MM-WMS-2 3,2 (EX5)R C1 WH/BK - 0803927



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 1.6 ... 3.2 mm, lettering field size: continuous x 5 mm

Shrink sleeve - MM-WMS-2 4,8 (EX9)R C1 WH/BK - 0803928



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 2.4 ... 4.8 mm, lettering field size: continuous x 9 mm

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Shrink sleeve - MM-WMS-2 6,4 (EX10)R C1 WH/BK - 0803929



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 3.2 ... 6.4 mm, lettering field size: continuous x 10 mm

Shrink sleeve - MM-WMS-2 9,5 (EX16)R C1 WH/BK - 0803930



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 4.8 ... 9.5 mm, lettering field size: continuous x 16 mm

Shrink sleeve - MM-WMS 3,2 (EX5)R C1 YE/BK - 1116139



Shrink sleeve, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: slide-on, cable diameter range: 1 ... 3.2 mm, lettering field size: continuous x 3.1 mm

Shrink sleeve - MM-WMS 4,8 (EX9)R C1 YE/BK - 1116140



Shrink sleeve, Roll, yellow/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: slide-on, cable diameter range: 1.6 ... 4.8 mm, lettering field size: continuous x 5.4 mm

Terminal marking

Label - MM-TML (EX3,8)R C1 WH/BK - 1092026



Label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, for terminal block width: 8000 mm, lettering field size: continuous x 3.8 mm

Thermal transfer printer - THERMOMARK GO - 1090747

Accessories

Label - MM-TML (EX4,2)R C1 TR/BK - 0803979



Label, Roll, transparent, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, for terminal block width: 8000 mm, lettering field size: continuous x 4.2 mm

Label - MM-TML (EX9,5)R C1 TR/BK - 0803981



Label, Roll, transparent, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, for terminal block width: 8000 mm, lettering field size: continuous x 9.5 mm

Label - MM-TMT (EX6,35)R C1 WH/BK - 0803982



Label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snap into universal marker groove, snap into flat marker groove, for terminal block width: 5500 mm, lettering field size: continuous x 6.35 mm

Label - MM-TMT (EX9,5)R C1 WH/BK - 0803983



Label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snap into universal marker groove, snap into flat marker groove, for terminal block width: 5500 mm, lettering field size: continuous x 9.5 mm