

Thermal transfer printer - THERMOMARK GO.K - 1184146

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Mobile thermal transfer printer for marking materials in cartridge format. The printer can print materials in continuous format up to a material width of 24 mm.

Product Description


The THERMOMARK GO.K handheld printer is ideal for fast marking on site. The thermal transfer printer is robust, easy to use, and offers versatile functions. It processes continuous media for terminal marking, cable and wire marking, equipment marking, and plant marking.

Your advantages

- ✓ Maintenance-free operation with proven thermal transfer printing technology
- ✓ Alternative, easy control with PROJECT COMPLETE software
- ✓ Printing of self-adhesive and non-adhesive labels as well as shrink sleeves
- ✓ The THERMOMARK GO.K prints materials in cartridge format, which contain the material to be marked and the appropriate ink ribbon.
- ✓ Intuitive user guidance thanks to a well-structured menu and direct input keys
- ✓ 8 different bar codes and over 300 symbols can be integrated; up to 20 projects can be created and stored directly on the device.



Key Commercial Data

Packing unit	1 pc
GTIN	 4 063151 223441
GTIN	4063151223441
Weight per Piece (excluding packing)	667.000 g
Weight per piece (including packing)	846.000 g
Custom tariff number	84433210
Country of origin	China
Sales Key	N1 - Printer+autom.Tools

Technical data

General

Interface	USB
Weight	667 g

Thermal transfer printer - THERMOMARK GO.K - 1184146

Technical data

Dimensions

Length	230 mm
Height	69 mm
Width	98 mm

Connection data

Minimum voltage	100 V AC
Max. voltage	240 V AC
Additional text	50 Hz ... 60 Hz

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 4.0	24010400
eCl@ss 4.1	24010400
eCl@ss 5.0	19020200
eCl@ss 5.1	19020200
eCl@ss 6.0	19140100
eCl@ss 7.0	19140104
eCl@ss 9.0	19140104

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001672
ETIM 6.0	EC001672
ETIM 7.0	EC001672

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43212108
UNSPSC 18.0	43212108
UNSPSC 19.0	43212108
UNSPSC 20.0	43212108
UNSPSC 21.0	43212108

Thermal transfer printer - THERMOMARK GO.K - 1184146

Accessories

Accessories

Conductor marking

Cable marker label - MM-WML 3 (EX10)R C1 WH/BK - 0803931



Cable marker label, Roll, white, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K: without print, mounting type: adhesive, lettering field size: continuous x 10 mm

Cable marker label - MM-WML 5 (EX10)R C1 WH/BK - 0803932



Cable marker label, Roll, white, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K: without print, mounting type: adhesive, lettering field size: continuous x 10 mm

Device marking

Label, highly flexible - MM-EMLF (EX18)R C1 GN/WH - 0803953



Label, highly flexible, Roll, green, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Label, highly flexible - MM-EMLF (EX24)R C1 GN/WH - 0803954



Label, highly flexible, Roll, green, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 24 mm

Label, highly flexible - MM-EMLF (EX10)R C1 OG/BK - 0803955



Label, highly flexible, Roll, orange, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Thermal transfer printer - THERMOMARK GO.K - 1184146

Accessories

Label, highly flexible - MM-EMLF (EX12)R C1 OG/BK - 0803956



Label, highly flexible, Roll, orange, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Label, highly flexible - MM-EMLF (EX18)R C1 OG/BK - 0803957



Label, highly flexible, Roll, orange, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Label, highly flexible - MM-EMLF (EX24)R C1 OG/BK - 0803958



Label, highly flexible, Roll, orange, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 24 mm

Label, highly flexible - MM-EMLF (EX10)R C1 RD/WH - 0803959



Label, highly flexible, Roll, red, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Fabric label - MM-EMLC (EX10)R C1 WH/BK - 0803933



Fabric label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Thermal transfer printer - THERMOMARK GO.K - 1184146

Accessories

Fabric label - MM-EMLC (EX12)R C1 WH/BK - 0803934



Fabric label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Fabric label - MM-EMLC (EX18)R C1 WH/BK - 0803936



Fabric label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Label, highly flexible - MM-EMLF (EX10)R C1 WH/BK - 0803937



Label, highly flexible, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Label, highly flexible - MM-EMLF (EX12)R C1 WH/BK - 0803938



Label, highly flexible, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Label, highly flexible - MM-EMLF (EX18)R C1 WH/BK - 0803939



Label, highly flexible, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Thermal transfer printer - THERMOMARK GO.K - 1184146

Accessories

Label, highly flexible - MM-EMLF (EX24)R C1 WH/BK - 0803940



Label, highly flexible, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 24 mm

Label, highly flexible - MM-EMLF (EX10)R C1 YE/BK - 0803941



Label, highly flexible, Roll, yellow, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Label, highly flexible - MM-EMLF (EX12)R C1 YE/BK - 0803942



Label, highly flexible, Roll, yellow, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Label, highly flexible - MM-EMLF (EX18)R C1 YE/BK - 0803943



Label, highly flexible, Roll, yellow, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Label, highly flexible - MM-EMLF (EX24)R C1 YE/BK - 0803944



Label, highly flexible, Roll, yellow, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 24 mm

Thermal transfer printer - THERMOMARK GO.K - 1184146

Accessories

Label, highly flexible - MM-EMLF (EX10)R C1 BU/WH - 0803945



Label, highly flexible, Roll, blue, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Label, highly flexible - MM-EMLF (EX12)R C1 BU/WH - 0803946



Label, highly flexible, Roll, blue, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Label, highly flexible - MM-EMLF (EX18)R C1 BU/WH - 0803947



Label, highly flexible, Roll, blue, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Label, highly flexible - MM-EMLF (EX24)R C1 BU/WH - 0803949



Label, highly flexible, Roll, blue, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 24 mm

Label, highly flexible - MM-EMLF (EX10)R C1 GN/WH - 0803950



Label, highly flexible, Roll, green, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Thermal transfer printer - THERMOMARK GO.K - 1184146

Accessories

Label, highly flexible - MM-EMLF (EX12)R C1 GN/WH - 0803952



Label, highly flexible, Roll, green, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Label, highly flexible - MM-EMLF (EX12)R C1 RD/WH - 0803960



Label, highly flexible, Roll, red, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Label, highly flexible - MM-EMLF (EX18)R C1 RD/WH - 0803961



Label, highly flexible, Roll, red, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Label, highly flexible - MM-EMLF (EX24)R C1 RD/WH - 0803962



Label, highly flexible, Roll, red, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 24 mm

Insert label - MM-EMT (EX6)R C1 WH/BK - 0803963



Insert label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snapped into marker carrier, lettering field size: continuous x 6 mm

Thermal transfer printer - THERMOMARK GO.K - 1184146

Accessories

Insert label - MM-EMT (EX8)R C1 WH/BK - 0803965



Insert label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snapped into marker carrier, lettering field size: continuous x 8 mm

Insert label - MM-EMT (EX15)R C1 WH/BK - 0803966



Insert label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snapped into marker carrier, lettering field size: continuous x 15 mm

Insert label - MM-EMT (EX17)R C1 WH/BK - 0803967



Insert label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snapped into marker carrier, lettering field size: continuous x 17 mm

Insert label - MM-EMT (EX18)R C1 WH/BK - 0803968



Insert label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snapped into marker carrier, lettering field size: continuous x 18 mm

Insert label - MM-EMT (EX23)R C1 WH/BK - 0803969



Insert label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snapped into marker carrier, lettering field size: continuous x 23 mm

Thermal transfer printer - THERMOMARK GO.K - 1184146

Accessories

Label - MM-EML (EX10)R C1 WH/BK - 0803970



Label, Roll, white/black, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Label - MM-EML (EX12)R C1 WH/BK - 0803971



Label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Label - MM-EML (EX18)R C1 WH/BK - 0803972



Label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Label - MM-EML (EX24)R C1 WH/BK - 0803973



Label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 24 mm

Label - MM-EML (EX10)R C1 SR/BK - 0803974



Label, Roll, silver, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 10 mm

Thermal transfer printer - THERMOMARK GO.K - 1184146

Accessories

Label - MM-EML (EX12)R C1 SR/BK - 0803975



Label, Roll, silver, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 12 mm

Label - MM-EML (EX18)R C1 SR/BK - 0803976



Label, Roll, silver, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 18 mm

Label - MM-EML (EX24)R C1 SR/BK - 0803978



Label, Roll, silver, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, lettering field size: continuous x 24 mm

Printing system accessories

Case - THERMOMARK GO CASE - 1229456



Practical and robust case for storing the THERMOMARK GO and THERMOMARK GO.K mobile printers as well as necessary accessories. The case provides space for nine material cartridges.

Transport bag - THERMOMARK GO.K BAG - 0805003



Shoulder bag for storing the THERMOMARK GO.K / THERMOFOX mobile printer as well as necessary accessory parts

Thermal transfer printer - THERMOMARK GO.K - 1184146

Accessories

Fastening clip - THERMOMARK GO.K BELT CLIP - 0805004



Clip for fastening the THERMOMARK GO.K / THERMOFOX mobile printer to a belt.

Mounting unit - THERMOMARK GO.K MAGNET HOLDER - 0805008



Magnetic holder for mounting the THERMOMARK GO.K / THERMOFOX mobile printer on metal surfaces, such as a control cabinet.

Battery - THERMOFOX/ACCU - 0805009



Battery for mobile operation of the THERMOMARK GO and THERMOMARK GO.K / THERMOFOX printers.

Power supply unit - THERMOFOX/ADAPTER - 0805010



Power supply unit incl. 4 adapters for operation of the THERMOMARK GO and THERMOMARK GO.K / THERMOFOX printers.

Charging tray - THERMOFOX/CHARGER - 0805012



Charging cradle for charging the THERMOFOX/ACCU battery (0805009), which is required for mobile operation of the THERMOMARK GO and THERMOMARK GO.K / THERMOFOX printers.

Shrink sleeve

Thermal transfer printer - THERMOMARK GO.K - 1184146

Accessories

Shrink sleeve - MM-WMS 3,2 (EX5)R C1 WH/BK - 0803923



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 1 ... 3.2 mm, lettering field size: continuous x 5 mm

Shrink sleeve - MM-WMS 4,8 (EX9)R C1 WH/BK - 0803924



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 1.6 ... 4.8 mm, lettering field size: continuous x 9 mm

Shrink sleeve - MM-WMS 6,4 (EX10)R C1 WH/BK - 0803925



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 2.1 ... 6.4 mm, lettering field size: continuous x 10 mm

Shrink sleeve - MM-WMS 9,5 (EX16)R C1 WH/BK - 0803926



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 3.2 ... 9.5 mm, lettering field size: continuous x 16 mm

Shrink sleeve - MM-WMS-2 3,2 (EX5)R C1 WH/BK - 0803927



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 1.6 ... 3.2 mm, lettering field size: continuous x 5 mm

Thermal transfer printer - THERMOMARK GO.K - 1184146

Accessories

Shrink sleeve - MM-WMS-2 4,8 (EX9)R C1 WH/BK - 0803928



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 2.4 ... 4.8 mm, lettering field size: continuous x 9 mm

Shrink sleeve - MM-WMS-2 6,4 (EX10)R C1 WH/BK - 0803929



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 3.2 ... 6.4 mm, lettering field size: continuous x 10 mm

Shrink sleeve - MM-WMS-2 9,5 (EX16)R C1 WH/BK - 0803930



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: slide-on, cable diameter range: 4.8 ... 9.5 mm, lettering field size: continuous x 16 mm

Terminal marking

Label - MM-TML (EX4,2)R C1 TR/BK - 0803979



Label, Roll, transparent, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, for terminal block width: 8000 mm, lettering field size: continuous x 4.2 mm

Label - MM-TML (EX9,5)R C1 TR/BK - 0803981



Label, Roll, transparent, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, for terminal block width: 8000 mm, lettering field size: continuous x 9.5 mm

Thermal transfer printer - THERMOMARK GO.K - 1184146

Accessories

Label - MM-TMT (EX6,35)R C1 WH/BK - 0803982



Label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snap into universal marker groove, snap into flat marker groove, for terminal block width: 5500 mm, lettering field size: continuous x 6.35 mm

Label - MM-TMT (EX9,5)R C1 WH/BK - 0803983



Label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: snap into universal marker groove, snap into flat marker groove, for terminal block width: 5500 mm, lettering field size: continuous x 9.5 mm

Label - MM-TML (EX3,8)R C1 WH/BK - 1092026



Label, Roll, white, unlabeled, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, for terminal block width: 8000 mm, lettering field size: continuous x 3.8 mm
