





Product no.: 2422EA

Ergonomic cutters, 5", TAPERED HEAD



Tapered head, rounded tip

Its thin, relieved head allows for easy access to hard-to-reach areas.

source images

The Perfect Cut - Strong, sharp and precise, every time

The Weller Erem Series 2400 Magic Sense is a range of medium-sized precision cutters that combines robustness, visibility and accessibility. A large variety of head shapes for precision work in hard-to-reach areas. The optimized ergonomic shape of the Series 2400 MagicSense prevents hand fatigue. These cutters are manufactured from improved induction-hardened cutting edges up to 64 – 65 HRc for an extremely long service life. The cutting edges are made from special tool steel. The precision cutters have a nonreflecting surface, are ESD safe and resharpenable.

	Туре	Type of Cut		Cutt	ing	Ca	pac	ity														
Series 240	00 Magic	Sense		0,03 0,1						0,7 .027	0,8 .031	0,9 .035	1,0 .039	1,1 .043	1,2 .047	1,3 .051	1,4 .055	1,5 .059		1,7 .066	1,8 .070	2,0 .078
E	2412E	Semi Flush																				
	2422E	Flush																				
	2432E	Super Full	Flush																			
0	2477E	Flush																				
191	2403E	Flush																	-			
	2404E	Flush																				
191	2482E	Flush																				
	2475E	Flush							-													
19	2470E	Flush							-													
	2476TX2	Flush / Car	bide																			











Technical Data	
Length mm	130
Length of cutting edges mm	11
Head width mm	11
Head thickness mm	6
Head length mm	18
Max. cutting capability – hard wire mm	
Weight in oz	2.575
Length of cutting edges Inches	0.433
Head width Inches	0.433
Head thickness Inches	0.236
Head length Inches	0.709
ESD-safe	on
Cut	Flush
Max. cutting capability – medium hardness mm	1
Max. cutting capability – copper wire mm	1.5
Length inches	5.118
Weight in g	73

Weller Tools GmbH Carl-Benz-Straße 2 74354 Besigheim Germany Phone: +49 (0) 7143 / 580-0 Fax.: +49 (0) 7143 / 580-108 Email: info@weller-tools.com Web: www.weller-tools.com