


LED Maschinenleuchte
 LED machine luminaire

 TUBELED_40 II Integrated,
 395 mm x 74 mm x 3 mm

Artikel-Nr.:	151110-01
EAN:	4260556623955
Zolltarifnr.:	94054099

Bestellnr.:	151110-01
Modell:	TUBELED_40 II Integrated
Bauform:	LED Einbauleuchte
Leuchtmittel:	SMD LED
Lampenleistung:	~16 W
Lampenlichtstrom:	2139 lm
Lampenlichtausbeute:	131 lm/W
Lichtverteilung:	Light Forming Technology
Lichtfarbe:	Tageslichtweiß (5200 - 5700K)
Anschlusswert Leuchte:	24V DC ± 10%
Anschluss Leuchte:	M12 A-kodiert
Schutzart:	IP67/IP69K
Schutzklasse:	III
Entblendung:	Diffusor ESG
Abstrahlwinkel:	100°
Betriebstemperatur:	-30... +60 °C
Farbwiedergabe (Ra):	> 85
Lampenlebensdauer:	> 60.000 h
Material Gehäuse:	Aluminium
Material Abdeckung:	Sicherheitsglas, 4 mm
Höhe [B] x Breite [C]:	32 mm x 74 mm, Blende 3 mm aufbauend
Länge [A]:	395 mm
Gewicht:	700 g
Bruttogewicht:	950 g
Risikogruppe:	freie Gruppe
Kennzeichnung:	CE
Dimmbar:	optional über Zubehör
Gefertigt in:	Deutschland
Besonderheit:	100% CNC geeignet


 TUBELED_40 II Integrated 151110-01
 TUBELED_40 II Integrated RGB-W 151190-01

Lampenlebensdauer in Betriebsstunden (L80/B10)


LED Maschinenleuchte
LED machine luminaire



Recessed luminaire TUBELED_40 II Integrated,
395 mm x 74 mm x 3 mm

Item number:	151110-01
EAN:	4260556623955
Customs tariff number:	94054099

Order number:	151110-01
Model:	TUBELED_40 II Integrated
Type:	LED recessed luminaire
Illuminant:	SMD LED
Power consumption:	~16 W
Lamp luminous flux:	2139 lm
Lamp luminous efficiency:	131 lm/W
Light distribution:	Light Forming Technology
Light colour:	daylight white (5200 - 5700K)
Connected load:	24V DC ± 10%
Connection (connector):	M12 A-type encoded
Degree of protection:	IP67/IP69K
Class of protection:	III
Glare-free	diffused safety glass
Beam angle (optics):	100°
Operating temperature:	-30... +60 °C
Colour rendering (Ra):	> 85
Lamps lifetime:	> 60,000 h
Housing material:	aluminium
Cover material:	Safety glass, 4 mm
Height [B] x Width [C]:	32 mm x 74 mm, Cover plate 3 mm externally
Length [A]:	395 mm
Weight (net):	700 g
Gross weight:	950 g
Risk group (DIN EN 62471):	free group
Marking:	CE
Dimmable:	via optional accessory
Made in:	Germany
Feature:	100% CNC approved



TUBELED_40 II Integrated 151110-01
TUBELED_40 II Integrated RGB-W 151190-01

Lamps lifetime in operation hours (L80/B10)