

**LED Maschinenleuchte**  
*LED machine luminaire*

**LEANLED II, 760 mm, opalweiÙe Abdeckung**

<b>Artikel-Nr.:</b>	111010-15
<b>EAN:</b>	4260556624112
<b>Zolltarifnr.:</b>	94054099
<b>Bestellnr.:</b>	111010-15
<b>Modell:</b>	LEANLED II
<b>Bauform:</b>	LED Aufbauleuchte
<b>Leuchtmittel:</b>	SMD LED
<b>Lampenleistung:</b>	~19 W
<b>Lampenlichtstrom:</b>	2835 lm
<b>Lampenlichtausbeute:</b>	145 lm/W
<b>Lichtverteilung:</b>	direkt
<b>Lichtfarbe:</b>	TageslichtweiÙ (5200 - 5700K)
<b>Anschlusswert Leuchte:</b>	24V DC ± 10%
<b>Anschluss Leuchte:</b>	M12 A-kodiert
<b>Schutzart:</b>	IP54
<b>Schutzklasse:</b>	III
<b>Entblendung:</b>	opalweiÙ
<b>Abstrahlwinkel:</b>	120°
<b>Betriebstemperatur:</b>	-10... +60 °C
<b>Farbwiedergabe (Ra):</b>	> 85
<b>Lampenlebensdauer:</b>	> 60.000 h
<b>Material Gehäuse:</b>	Aluminium
<b>Material Abdeckung:</b>	Polycarbonat, matt
<b>Höhe [B] x Breite [C]:</b>	31 mm x 26 mm
<b>Länge [A]:</b>	760 mm
<b>Gewicht:</b>	500 g
<b>Bruttogewicht:</b>	800 g
<b>Risikogruppe:</b>	freie Gruppe
<b>Kennzeichnung:</b>	CE, ETL Listed
<b>Befestigungszubehö:</b>	2 Paar Halterungen (drehbare oder planare Befestigung) im Lieferumfang
<b>Dimmbar:</b>	optional über Zubehö
<b>Gefertigt in:</b>	Deutschland



Lampenlebensdauer in Betriebsstunden (L80/B10)

LED Maschinenleuchte  
*LED machine luminaire*



**LEANLED II, 760 mm, opal white cover**

<b>Item number:</b>	111010-15
<b>EAN:</b>	4260556624112
<b>Customs tariff number:</b>	94054099

<b>Order number:</b>	111010-15
<b>Model:</b>	LEANLED II
<b>Type:</b>	LED surface-mounted luminaire
<b>Illuminant:</b>	SMD LED
<b>Power consumption:</b>	~19 W
<b>Lamp luminous flux:</b>	2835 lm
<b>Lamp luminous efficiency:</b>	145 lm/W
<b>Light distribution:</b>	direct
<b>Light colour:</b>	daylight white (5200 - 5700K)
<b>Connected load:</b>	24V DC $\pm$ 10%
<b>Connection (connector):</b>	M12 A-type encoded
<b>Degree of protection:</b>	IP54
<b>Class of protection:</b>	III
<b>Glare-free</b>	opal white
<b>Beam angle (optics):</b>	120°
<b>Operating temperature:</b>	-10... +60 °C
<b>Colour rendering (Ra):</b>	> 85
<b>Lamps lifetime:</b>	> 60,000 h
<b>Housing material:</b>	aluminium
<b>Cover material:</b>	Polycarbonate, soft
<b>Height [B] x Width [C]:</b>	31 mm x 26 mm
<b>Length [A]:</b>	760 mm
<b>Weight (net):</b>	500 g
<b>Gross weight:</b>	800 g
<b>Risk group (DIN EN 62471):</b>	free group
<b>Marking:</b>	CE, ETL Listed
<b>Mounting accessories:</b>	2 pairs mounting holders (holder for swivel or planar mounting) in delivery scope
<b>Dimmable:</b>	via optional accessory
<b>Made in:</b>	Germany



Lamps lifetime in operation hours (L80/B10)