

LED Maschinenleuchte
LED machine luminaire

**LEANLED II, 260 mm, klare Abdeckung,
 kaskadierbar**

| | |
|----------------------|---------------|
| Artikel-Nr.: | 111010-22 |
| EAN: | 4260556624150 |
| Zolltarifnr.: | 94054099 |

| | |
|-------------------------------|--|
| Bestellnr.: | 111010-22 |
| Modell: | LEANLED II |
| Bauform: | LED Aufbauleuchte |
| Leuchtmittel: | SMD LED |
| Lampenleistung: | ~6 W |
| Lampenlichtstrom: | 945 lm |
| Lampenlichtausbeute: | 145 lm/W |
| Lichtverteilung: | direkt |
| Lichtfarbe: | Tageslichtweiß (5200 - 5700K) |
| Anschlusswert Leuchte: | 24V DC ± 10% |
| Anschluss Leuchte: | M12 A-kodiert |
| Schutzart: | IP54 |
| Schutzklasse: | III |
| Abstrahlwinkel: | 120° |
| Betriebstemperatur: | -10... +60 °C |
| Farbwiedergabe (Ra): | > 85 |
| Lampenlebensdauer: | > 60.000 h |
| Material Gehäuse: | Aluminium |
| Material Abdeckung: | Polycarbonat, klar, splitterfrei |
| Höhe [B] x Breite [C]: | 31 mm x 26 mm |
| Länge [A]: | 260 mm |
| Gewicht: | 200 g |
| Bruttogewicht: | 350 g |
| Risikogruppe: | freie Gruppe |
| Kennzeichnung: | CE, ETL Listed |
| Befestigungszubehör: | 2 Paar Halterungen (drehbare oder planare Befestigung) im Lieferumfang |
| Dimmbar: | optional über Zubehör |
| Gefertigt in: | Deutschland |
| Besonderheit: | kaskadierbar, mehrere Leuchten lassen sich bis zu einer Gesamtstromstärke von max. 4A elektrisch verketteten |



Lampenlebensdauer in Betriebsstunden (L80/B10)

LED Maschinenleuchte
LED machine luminaire



**LEANLED II, 260 mm, clear cover,
cascadable**

| | |
|-------------------------------|---------------|
| Item number: | 111010-22 |
| EAN: | 4260556624150 |
| Customs tariff number: | 94054099 |

| | |
|-----------------------------------|--|
| Order number: | 111010-22 |
| Model: | LEANLED II |
| Type: | LED surface-mounted luminaire |
| Illuminant: | SMD LED |
| Power consumption: | ~6 W |
| Lamp luminous flux: | 945 lm |
| Lamp luminous efficiency: | 145 lm/W |
| Light distribution: | direct |
| Light colour: | daylight white (5200 - 5700K) |
| Connected load: | 24V DC \pm 10% |
| Connection (connector): | M12 A-type encoded |
| Degree of protection: | IP54 |
| Class of protection: | III |
| Beam angle (optics): | 120° |
| Operating temperature: | -10... +60 °C |
| Colour rendering (Ra): | > 85 |
| Lamps lifetime: | > 60,000 h |
| Housing material: | aluminium |
| Cover material: | polycarbonat, clear, shatterproof |
| Height [B] x Width [C]: | 31 mm x 26 mm |
| Length [A]: | 260 mm |
| Weight (net): | 200 g |
| Gross weight: | 350 g |
| Risk group (DIN EN 62471): | free group |
| Marking: | CE, ETL Listed |
| Mounting accessories: | 2 pairs mounting holders (holder for swivel or planar mounting) in delivery scope |
| Dimmable: | via optional accessory |
| Made in: | Germany |
| Feature: | cascadable, several luminaires can be interlinked electrically. The entire power consumption may not exceed 4A DC. |



Lamps lifetime in operation hours (L80/B10)