

LED Signalleuchte
 LED signal luminaire

SIGNALLED II RGB, 260 mm

Artikel-Nr.:	111090-12
EAN:	4260556624488
Zolltarifnr.:	94054099

Bestellnr.:	111090-12
Modell:	SIGNALLED II RGB
Bauform:	LED Aufbauleuchte
Leuchtmittel:	RGB LED
Lampenleistung Rot:	~2,6 W
Lampenleistung Grün:	~2,6 W
Lampenleistung Blau:	~2,6 W
Lampenlichtstrom Rot:	59 lm
Lampenlichtstrom Grün:	27 lm
Lampenlichtstrom Blau:	93 lm
Lichtverteilung:	direkt
Lichtfarbe:	RGB Farbraum (mindestens 2563 Farben)
Anschlusswert Leuchte:	24V DC - 10% +7% (RGB)
Anschluss Leuchte:	M12 Steckverbinder A-kodiert
Schutzart:	IP54
Schutzklasse:	III
Entblendung:	opalweiß
Abstrahlwinkel:	120°
Betriebstemperatur:	-10... +50 °C
Lampenlebensdauer:	> 60.000 h
Material Gehäuse:	Aluminium
Material Abdeckung:	Polycarbonat
Höhe [B] x Breite [C]:	25 mm x 30 mm
Länge [A]:	260 mm
Gewicht:	200 g
Bruttogewicht:	350 g
Risikogruppe:	freie Gruppe
Befestigungszubehör:	2 Paar Halterungen (inkl.)
Dimmbar:	nein
Kennzeichnung:	CE, ETL Listed
Gefertigt in:	Deutschland
Besonderheit:	Signalisieren über Blinken und/oder farbiges Licht



Lampenlebensdauer in Betriebsstunden (L80/B10)

LED Signalleuchte
LED signal luminaire



SIGNALLED II RGB, 260 mm

Item number:	111090-12
EAN:	4260556624488
Customs tariff number:	94054099

Order number:	111090-12
Model:	SIGNALLED II RGB
Type:	LED surface-mounted luminaire
Illuminant:	RGB LED
Power consumption RED:	~2,6 W
Power consumption GREEN:	~2,6 W
Power consumption BLUE:	~2,6 W
Lamp luminous flux RED:	59 lm
Lamp luminous flux GREEN:	27 lm
Lamp luminous flux BLUE:	93 lm
Light distribution:	direct
Light colour:	RGB colour space (at least 2563 colours)
Connected load:	24V DC - 10% +7% (RGB)
Connection (connector):	M12 A-type encoded
Degree of protection:	IP54
Class of protection:	III
Glare-free	opal white
Beam angle (optics):	120°
Operating temperature:	-10... +50 °C
Lamps lifetime:	> 60,000 h
Housing material:	aluminium
Cover material:	polycarbonate, soft
Height [B] x Width [C]:	25 mm x 30 mm
Length [A]:	260 mm
Weight (net):	200 g
Gross weight:	350 g
Risk group (DIN EN 62471):	free group
Mounting accessories:	2 pairs mounting holders (holder for swivel or planar mounting) pin delivery scope
Dimmable:	no
Marking:	CE, ETL Listed
Made in:	Germany
Feature:	Signalling via flashing and/or coloured light



Lamps lifetime in operation hours (L80/B10)