

LED Signalleuchte  
 LED signal luminaire

**SIGNALLED II RGB, 760 mm**

<b>Artikel-Nr.:</b>	111090-15
<b>EAN:</b>	4260556624518
<b>Zolltarifnr.:</b>	94054099

<b>Bestellnr.:</b>	111090-15
<b>Modell:</b>	SIGNALLED II RGB
<b>Bauform:</b>	LED Aufbauleuchte
<b>Leuchtmittel:</b>	RGB LED
<b>Lampenleistung Rot:</b>	~7,9 W
<b>Lampenleistung Grün:</b>	~7,9 W
<b>Lampenleistung Blau:</b>	~7,9 W
<b>Lampenlichtstrom Rot:</b>	177 lm
<b>Lampenlichtstrom Grün:</b>	81 lm
<b>Lampenlichtstrom Blau:</b>	279 lm
<b>Lichtverteilung:</b>	direkt
<b>Lichtfarbe:</b>	RGB Farbraum (mindestens 2563 Farben)
<b>Anschlusswert Leuchte:</b>	24V DC - 10% +7% (RGB)
<b>Anschluss Leuchte:</b>	M12 Steckverbinder A-kodiert
<b>Schutzart:</b>	IP54
<b>Schutzklasse:</b>	III
<b>Entblendung:</b>	opalweiß
<b>Abstrahlwinkel:</b>	120°
<b>Betriebstemperatur:</b>	-10... +50 °C
<b>Lampenlebensdauer:</b>	> 60.000 h
<b>Material Gehäuse:</b>	Aluminium
<b>Material Abdeckung:</b>	Polycarbonat
<b>Höhe [B] x Breite [C]:</b>	25 mm x 30 mm
<b>Länge [A]:</b>	760 mm
<b>Gewicht:</b>	500 g
<b>Bruttogewicht:</b>	800 g
<b>Risikogruppe:</b>	freie Gruppe
<b>Befestigungszubehör:</b>	2 Paar Halterungen (inkl.)
<b>Dimmbar:</b>	nein
<b>Kennzeichnung:</b>	CE, ETL Listed
<b>Gefertigt in:</b>	Deutschland
<b>Besonderheit:</b>	Signalisieren über Blinken und/oder farbiges Licht



Lampenlebensdauer in Betriebsstunden (L80/B10)

LED Signalleuchte  
LED signal luminaire



## SIGNALLED II RGB, 760 mm

<b>Item number:</b>	111090-15
<b>EAN:</b>	4260556624518
<b>Customs tariff number:</b>	94054099

<b>Order number:</b>	111090-15
<b>Model:</b>	SIGNALLED II RGB
<b>Type:</b>	LED surface-mounted luminaire
<b>Illuminant:</b>	RGB LED
<b>Power consumption RED:</b>	~7,9 W
<b>Power consumption GREEN:</b>	~7,9 W
<b>Power consumption BLUE:</b>	~7,9 W
<b>Lamp luminous flux RED:</b>	177 lm
<b>Lamp luminous flux GREEN:</b>	81 lm
<b>Lamp luminous flux BLUE:</b>	279 lm
<b>Light distribution:</b>	direct
<b>Light colour:</b>	RGB colour space (at least 2563 colours)
<b>Connected load:</b>	24V DC - 10% +7% (RGB)
<b>Connection (connector):</b>	M12 A-type encoded
<b>Degree of protection:</b>	IP54
<b>Class of protection:</b>	III
<b>Glare-free</b>	opal white
<b>Beam angle (optics):</b>	120°
<b>Operating temperature:</b>	-10... +50 °C
<b>Lamps lifetime:</b>	> 60,000 h
<b>Housing material:</b>	aluminium
<b>Cover material:</b>	polycarbonate, soft
<b>Height [B] x Width [C]:</b>	25 mm x 30 mm
<b>Length [A]:</b>	760 mm
<b>Weight (net):</b>	500 g
<b>Gross weight:</b>	800 g
<b>Risk group (DIN EN 62471):</b>	free group
<b>Mounting accessories:</b>	2 pairs mounting holders (holder for swivel or planar mounting) pin delivery scope
<b>Dimmable:</b>	no
<b>Marking:</b>	CE, ETL Listed
<b>Made in:</b>	Germany
<b>Feature:</b>	Signalling via flashing and/or coloured light



Lamps lifetime in operation hours (L80/B10)