





"Schutzvermerk nach DIN EN ISO 9000 beachten" "Please pay attention to copyright note DIN ISO 9000"



A-A (1 : 1)



ISO (1 : 2)



Stückliste / Part list					
Pos.	ST	Bezeichnung / description	Kurzbezeichnung / brief description	Werkstoff / Material	Sonstiges / Information
1	2	Profilsseitenwand / Profile side panel	BSW 22900	Al Mg Si 0,5 F22 E6/EV1	
2	2	Frontprofil / Front panel	PF 00084	Al Mg Si 0,5 F22 E6/EV1	
3	2	Busprofil / Bus panel	PB 00084	Al Mg Si 0,5 F22 E6/EV1	
4	1	Doppeltrantprofil / Double front profile	PFD 00084	Al Mg Si 0,5 F22 E6/EV1	
5	1	Doppelbusprofil / Double bus profile	PBD 00684	Al Mg Si 0,5 F22 E6/EV1	
6	1	Doppelrastprofil / Double snap profile	RPD 00384	Al Mg Si 0,5 F22 E6/EV1	
7	4	Gewindestreifen I (M2,5) / Tapped strip I (M2,5)	GS 00084-I	Stahl, verzinkt / Steel, zinc-plated	
8	4	Gewindestreifen II (M2,5) / Tapped strip II (M2,5)	GS 00084-II	Stahl, verzinkt / Steel, zinc plated	
9	8	Isolierstreifen / Insulated plastic	IS 00042	PA-UL 94 V1	
10	20	Zylinderschraube / Cheese head screw	SHR 2 M4x20 DIN 912	V2A	
11	20	Sicherungsscheibe, Securing washer	Schnorr "S4"	Stahl, geschwärzt / Steel, blackened	
12	10	Kartenführung / Card guide	KF 160	PA V0, grün / PA V0, green	symbolisch dargestellt / shown symbolic

Maßstab/
Scale: 1:1 (1:2)

Zeichnungs-Nr. / Drawing-No.:
OK 5045.34.74.01

Artikel / Article:
BGT 22680.Pi-BN

A Nr. /
Alt No.:

Datum/
Date:

DISK:

2904429.idw
Datum/Date: 09.07.2020 JL

BOPLA

A Phoenix Mecano Company