

# FULL HD Birdcam TX-165



- Ideal for recording and observing birds and small animals (short lens focus 6-15cm; big viewing angle of 100°)
- Slow motion videos with up to 25FPS
- Functions: video, photo, video & photo or slow motion
- PIR sensor (~20cm) & IR range (~50cm) with 940nm LEDs for night recordings
- Built-in microphone & speaker
- Removable bird food container for approx. 150g bird food
- Tit dumplings hook
- Removable water basin

### Technical specifications

- Image sensor: 1/3.2" CMOS 8MP
- Lens focus: Fixed 0.06-0.15m
- Lens: f=2.0mm, F/NO2.0, FOV=100°, Auto IR filter; (scratchproof and shockproof)
- Video resolution: [1920x1080] / [1280x720] / [1280x720 60FPS] / [848x480] / [720x480] / [720x480 100FPS] / [640x480] / [320x240]
- Photo resolution: 20MP (5200x3900 interpolated), 16MP (4608x3456 interpolated), 12MP (4000x3000 interpolated), 8MP (3264x2448), 5MP (2592x1944), 3MP (2048x1536), 1MP (1280x960)
- File format JPEG / AV
- Infrared: 4x IR LEDs (940nm), 0.03-0.5m range
- Power supply: 4x AA batteries\* (\*included); external DC6V/1A\*\* (\*\*not included)
- Device language: EN, DE, SP, FR, IT, NL, FI, SE, DK, PO
- Working temperature: -10°C up to +50°C
- Material: ABS plastic
- Weight / Dimensions: 141g (without batteries)/(L) 8.7 x (W) 4.4 x (H) 10.7cm
- Weight / Dimensions House with seed box and basin: 475g / (L) 19 x (W) 15.2 x (H) 22.8cm

### Package Contents

Technaxx FULL HD Birdcam TX-165, Micro USB cable, mounting belt, wall mount, railing mount, 3x screws & 3x dowels, 4x AA batteries, User Manual



Article-No.4923

