






Funktionen 


- 4G (LTE)
- WhatsApp vorinstalliert
- SOS Notruftaste / Notruffunktion (GPS Optional)
- SOS Sicherheitszone (GPS)
- Einfache Bea-fon Bedieneroberfläche
- Touch Display 2.8" (7,1cm)
- Kamera: Rückseite 8.0MP Autofokus
- Kamera Front 5.0 MP
- Multimedia und Audio Player
- WLAN, Bluetooth
- Telefonbuch für bis zu 1000 Einträge
- FM Radio
- Fotokontakte
- Freisprechfunktion
- Tischladeschale im Lieferumfang

Functions 

- 4G (LTE)
- WhatsApp pre-installed
- SOS emergency call button / emergency call (GPS)
- SOS safety zone (GPS)
- Simple Bea-fon user interface
- 2.8 "(7.1cm) touch display
- Camera: Rear 8.0MP auto focus
- Front camera 5.0 MP
- Multimedia and audio player
- WLAN, Bluetooth
- Telephone book for up to 1000 entries
- FM radio
- Photo contacts
- Hands-free function
- Desktop charger included

Les fonctions 

- 4G (LTE)
- WhatsApp pré-installé
- Bouton d'appel d'urgence SOS / (GPS en option)
- Zone de sécurité SOS (GPS)
- Interface utilisateur simple de Bea-fon
- Écran tactile de 2,8 po (7,1 cm)
- Caméra: mise au point automatique arrière 8,0MP
- Caméra frontale 5,0 MP
- Lecteur multimédia et audio
- WLAN, Bluetooth
- Annuaire téléphonique jusqu'à 1000 entrées
- Radio FM
- Contacts photo
- Fonction mains libres
- Chargeur de bureau inclus

Funzioni 

- 4G (LTE)
- WhatsApp preinstallato
- chiamata di emergenza SOS / funzione di chiamata di emergenza (GPS opzionale)
- Zona di sicurezza SOS (GPS)
- Semplice interfaccia utente Bea-fon
- Display a sfioramento da 2,8 "(7,1 cm)
- Fotocamera: 8,0 MP fuoco automatica
- Fotocamera frontale 5,0 MP
- Lettore multimediale e audio
- WLAN, Bluetooth
- Rubrica telefonica fino a 1000 voci
- FM Radio
- Contatti foto
- Funzione vivavoce
- Caricatore da tavolo incluso

Specifications	
Type	Clamshell phone
Colour	Black - Piano lacquer
Size in mm (L x W x D)	108x56.5x20.5
Weight in grams	130
Standby time in hours	180
Talk time in minutes	220
Battery	Li-ion 3.7V - 1400mAh
Charger	5V-10 00mA
Micro USB port	2.0
Processor	Quadcore 1.5GHz
Memory (RAM/ROM)	512MB/4GB
2G Band (MHz)	900/1800
3G Band (MHz)	900/2100
4G Band (VoLTE)	B1/B3/B7/B8/B20/
SAR Head	0.215 W/kg
SAR Body	1.754 W/kg
SIM card slot	Micro
Backlight keypad	✓

Display	
Type	TFT colour touch display
Colours	65,000
Resolution	240x320
Dimensions	2.8"
Backlight	✓
Clock	✓
Date	✓

Tones and signals	
Profiles incl. all tone settings	✓
Ringtones	✓
Vibration alarm	✓
Human voice tone of key numbers	✓
Volume side key	✓

SOS/safety	
Emergency call button	✓
SOS - SMS	✓
SOS - numbers	5
SOS - signal tone	✓
SOS - positioning via sms	✓
SOS - Secure zone	✓
Low battery sms alarm	

Call	
Phone numbers in phonebook	1000
Volume control	✓
Hands-free function	✓
Speaker volume control	✓
Mute	✓
Call duration	✓
Conference call	✓
Headset port	3.5 jack
Call volume decibel (distance 1cm)	<40
Ring volume decibel (distance 1m)	<85

Call list	
Incoming calls	100
Missed calls	100
Dialled calls	100
Call duration	✓

Messaging	
Text mode	Smart, ABC, abc, 123
Virtual keypad (optional)	QUERTY

Network services	
Caller ID	✓
Call waiting	✓
Forward (all) calls	✓
Forward call if not reachable	✓
Forward call if not accepted	✓
Forward call if busy	✓
Forward (all) data	✓
Manual/automatic network selection	✓

Safety	
Lock phone	✓
Screen Lock	✓
Turn SIM PIN on/off	✓
Change SIM PIN	✓
Reset to default settings	✓

Extras	
Phone languages	EN/DE/FR/IT/ES/NL/ FI/SV
User guides languages	DE/EN/FR/IT/NL
Alarm	✓
Reminders	✓
Calculator	✓
FM radio/audio player / video player ✓	✓
Positioning (GPS)	✓
Speed dial keys (2-9)	✓
Photo contacts	✓
LED torch	✓
AppStore	✓
WhatsApp preinstalled	✓
Web browser	✓
File manager	✓
WLAN	Wi-Fi 4 (a/b/g/n)
Bluetooth	4.2
Extra key for Camera	✓
Camera	8.0 MP
Front- camera	5.0MP
Micro SD card slot	Up to 128 GB

Package	
Mobile phone	✓
Battery	✓
Power adapter	✓
Table charger	✓
USB cable	✓
User guide	DE/FR/IT
WhatsApp quick guide	DE/FR/IT