

/ MACSTOPAC 300 S3 HIGH / 67153 / EN ISO 20345:2011 S3 HRO SRC //



APPLICATIONS //

versatile model for demanding work environments, construction, industry, heavy industry, hot ground, humid environments

TECHNICAL SPECIFICATIONS //

- **sole:** MACSOLE® PLUS 2.0 rubber sole | excellent grip | hydrocarbon and chemical resistant | inert to hydrolysis | resistant to contact heat up to 300°C | rubber-covered toe cap | EVA inserts in forefoot and heel for an excellent shock absorption
- **upper:** water-resistant grain leather | few seams | padded collar
- **lining:** Distance-Mesh | excellent abrasion resistance | very high moisture absorption capacity | quick drying
- **toe cap:** metal free
- **penetration-resistant midsole:** metal free
- **hygienic insole:** removable | anatomical | bottom layer open cell foam: very high moisture absorption capacity, fast drying
- **sizes:** 37 - 48
- **weight:** 690 g in size 42
- French (EU) sizing system | width 11