



| PART NUMBER | DIM L (INCH)    | DIM L (mm)      |
|-------------|-----------------|-----------------|
| 73726-0000  | .375±.015       | 9.50±0.38       |
| 73726-0005  | .300+.015/-.030 | 7.62+0.38/-0.76 |
| 73726-0015  | .250±.030       | 6.35±0.76       |

CROSS-RECESSED PAN HEAD



#2-32 TYPE AB SELF-TAPPING SCREW THREAD

NOTES:  
1. MATERIAL: STAINLESS STEEL, PASSIVATED.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

|  |        |  |            |   |  |  |
|--|--------|--|------------|---|--|--|
| DIMENSION UNITS                                      | SCALE  | CURRENT REV DESC: RESUME DIM L TOLERANCE +0.38/-0.76 FOR PN73726-0005 IN TABLE TO MEET MOLEX GENERAL REQUIREMENT |            | <b>molex</b>  |  |  |
| mm   | NTS    |  |            |   |  |  |
| GENERAL TOLERANCES (UNLESS SPECIFIED)                |        |  |            | SELF-TAPPING MOUNTING SCREW   |  |  |
| ANGULAR TOL  | ± 0.5° | EC NO: 682987  |            | PRODUCT CUSTOMER DRAWING  |  |  |
| 4 PLACES   | ±      | DRWN: YOGEEB   | 2021/10/27 | DOCUMENT NUMBER: <b>SD-73726-002</b> DOC TYPE: PSD DOC PART: 001 REVISION: B2 |  |  |
| 3 PLACES   | ±      | CHK'D: CWANG25   | 2021/10/27 |   |  |  |
| 2 PLACES   | ± 0.13 | APPR: SHONG  | 2021/11/11 | MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET SHEET NUMBER: 1 OF 1      |  |  |
| 1 PLACE  | ± 0.25 | INITIAL REVISION:  |            |   |  |  |
| 0 PLACES   | ±      | DRWN: MWOLFE   | 2012/03/09 |   |  |  |
| DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS |        | APPR: SMILLER  | 2012/03/12 |   |  |  |
|  |        | THIRD ANGLE PROJECTION   | DRAWING    | SERIES  |  |  |
|  |        |  | C-SIZE     | 73726   |  |  |

|                 |    |              |                     |
|-----------------|----|--------------|---------------------|
| DOCUMENT STATUS | P1 | RELEASE DATE | 2021/11/11 06:20:25 |
|-----------------|----|--------------|---------------------|