



brennenstuhl®

SICHERHEITSINFORMATIONEN

SAFETY INFORMATION

DE	Sicherheitsinformationen	HU	Biztonsági információk	LT	Saugos informacija
EN	Safety information	RU	Информация о безопасности	LV	Drošības informācija
FR	Informations sur la sécurité	TR	Güvenlik bilgileri	HR	Sigurnosne informacije
NL	Veiligheidsinformatie	FI	Turvallisuustiedot	RO	Informații privind siguranța
IT	Informazioni sulla sicurezza	GR	Πληροφορίες για την ασφάλεια	BG	Информация за безопасност
SE	Säkerhetsinformation	PT	Informações de segurança	DK	Oplysninger om sikkerhed
ES	Información de seguridad	EE	Ohutusalane teave	NO	Sikkerhetsinformasjon
PL	Informacje dotyczące bezpieczeństwa	SK	Bezpečnostné informácie	UA	Інформація з техніки безпеки
CZ	Bezpečnostní informace	SI	Varnostne informacije	AR	معلومات السلامة

WWW.BRENNENSTUHL.COM

04/11/2024



CE EAC

Art. 1 159780 615

**Hugo Brennenstuhl GmbH & Co. KG,
Seestr.1-3, D-72074 Tübingen**

lectra technik ag, Blegistrasse 13, CH-6340 Baar
service@brennenstuhl.com

4



007123

667659

4121 4623

0483917/4323



SDL PD 05 DE 4121 Art. 1 159780 615
1,5 m H05VV-F 3G1,5 0483916/2820
3680W MAX, 16A 230V~

USB type A port: 5,0V=2,4A MAX 12,0W, 9,0V=2,0A MAX 18,0W;
12,0V=1,5A MAX 18,0W

USB-PD: 5,0V=3,0A MAX 15,0W, 9,0V=3,0A MAX 27,0W;
15,0V=3,0A MAX 45,0W; 20,0V=2,25A MAX 45,0W

USB type A+A+USB-PD: 5,0V=4,8A MAX 24,0W for total
and 5,0V=2,4A MAX 12,0W for each

4121/4420
Made in China

