

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0008500105](#)  
**Status:** **Active**  
**Overview:** [KK Interconnect Solutions](#)  
**Description:** KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Brass Tin (Sn)

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-002-001 \(PDF\)](#)  
[Product Specification PS-08-50-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family Crimp Terminals  
 Series [2478](#)  
 Application Power, Wire-to-Board  
 Crimp Quality Equipment Yes  
 Overview [KK Interconnect Solutions](#)  
 Packaging Alternative [08500106](#) (Loose)  
 Product Name KK 396, KK 508  
 UPC 800753614437

**Physical**

Gender Female  
 Material - Metal Brass  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Net Weight 0.196/g  
 Packaging Type Reel  
 Plating min - Mating 2.540µm  
 Plating min - Termination 2.540µm  
 Termination Interface: Style Crimp or Compression  
 Wire Insulation Diameter 2.79mm max.  
 Wire Size AWG 18, 20, 22, 24  
 Wire Size mm<sup>2</sup> N/A

**Solder Process Data**

Lead-freeProcess Capability N/A

**Material Info**

Engineering Number 2478-1(P909)

**Reference - Drawing Numbers**

Packaging Specification [PK-2759-002-001](#)  
 Product Specification [PS-08-50-001](#)  
 Sales Drawing [SD-2478-001](#)



Series image - Reference only

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 D(2021)4569-DC (8  
 July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[2478](#) Series

**Use With**

[2574](#) , [2139](#) , [41695](#) , [3069](#) , [6422](#) , [5265](#) ,  
[5239](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
-------------	-----------

Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals	<a href="#">11030016</a>
---	--------------------------

Terminator Die	<a href="#">11402096</a>
----------------	--------------------------

Hand Crimp Tool for 3.96mm Pitch KK	<a href="#">638279500</a>
-------------------------------------	---------------------------

Crimp Terminals,  
18-24 AWG  
Mini-Mac Applicator [638885000](#)  
for KK and Trifurcon,  
3.96mm Terminals,  
18-24 AWG, check  
ATS for Wire  
Insulation Diameter  
Compatibility

**Japan**

<b>Description</b>	<b>Product #</b>
--------------------	------------------

Hand Extraction Tool	<a href="#">11260059</a>
----------------------	--------------------------

Hand Extraction Tool	<a href="#">570926000</a>
----------------------	---------------------------

This document was generated on 02/01/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**