

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022057055

Status:

Active

Overview:

Mini-SPOX Wire-to-Board Connector System

Description:

2.50mm Pitch, Mini-SPOX PCB Header, Single Row, Through Hole, Tin Plating, Friction Lock, 5 Circuits, Bag, 3.50mm PC Tail Length

Documents:

- Drawing (PDF)

2D Drawing DXF (PDF)

3D Model

3D Model (PDF)

2D Drawing (DXF)
- Product Specification 52641001-PS-000 (PDF)

Product Specification PS-5264-001-001 (PDF)

Packaging Specification SPK-5268-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

5268

Application

Signal, Wire-to-Board

Overview

Mini-SPOX Wire-to-Board Connector System

Product Name

Mini-SPOX

UPC

800753592797

Physical

Breakaway

No

Circuits (Loaded)

5

Circuits (maximum)

5

Color - Resin

Natural

Durability (mating cycles max)

30

First Mate / Last Break

No

Flammability

94V-0

Glow-Wire Capable

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Nylon

Net Weight

528.800/mg

Number of Rows

1

Orientation

Right Angle

PC Tail Length

3.50mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

2.50mm

Plating min - Mating

4.064µm

Plating min - Termination

4.064µm

Polarized to Mating Part

Yes

Polarized to PCB

No

Shrouded

Fully

Stackable

No

Surface Mount Compatible (SMC)

No

Temperature Range - Operating

-40° to +105°C



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

5268 Series

Mates With

Mini-SPOX Receptacle Housing 5264

Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	250V
Material Info	
Engineering Number	5268-05A
Reference - Drawing Numbers	
Packaging Specification	SPK-5268-001-001
Product Specification	52641001-PS-000, PS-5264-001-001
Sales Drawing	52680001-SD-000

This document was generated on 12/22/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION