

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200658655](#)
Status: **Active**
Overview: [Brad Micro-Change \(M12\) Connectors](#)
Description: Micro-Change (M12) Single-Ended Cordset, 3 Poles, Male (Straight) to Pigtail, 0.34mm² Black PUR LSOH Cable, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Industrial Cordsets
Series [120065](#)
Connector End A Micro-Change (M12)
Connector End B Pigtail
IP Rating IP67
Material - Contact Copper Alloy
Overview [Brad Micro-Change \(M12\) Connectors](#)
Product Name Micro-Change (M12)
Protocol N/A
Region Europe
Type Single Ended
UPC 78172514584

Physical

Cable Diameter 4.32mm (.170")
Cable Length 2.0m (6.56')
Color - Cable Jacket Black
Coupling Style Threaded
Gender Male-Pigtail
Keyway Single
LED Indicator No
Material - Cable Jacket PUR
Material - Connector Body PUR
Material - Coupling Nut Nickel-plated Brass
Material - Plating Mating Gold
Net Weight 66.382/g
Orientation Straight to Pigtail
Poles 3
Temperature Range - Operating -25° to +80°C
Wire Size AWG 22
Wire/Cable Type UL 21198

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 60V

Material Info

Engineering Number 803006H09M020

Reference - Drawing Numbers

Sales Drawing 1200659185-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[120065](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION