

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200850006

Status:

Active

Overview:

Brad Ultra-Lock Connection System

Description:

Ultra-Lock (M12) Single Keyway with PG9 Cable Fitting, Male, 5 Pole, Cable Diameter 4.10-8.10mm



Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
General	
Product Family	Field Attachable / Accessories
Series	120085
Approvals	cCSAus certified
IP Rating	IP69K
Material - Contact	Brass
Overview	Brad Ultra-Lock Connection System
Product Name	Ultra-Lock (M12)
Type	Field Attachable Connector
UPC	78172553193
Physical	
Cable Diameter	4.10-8.10mm (.161-.319")
Coupling Type	Push to Lock
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	Single
Material - Connector Body	PA
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	25.854/g
Orientation	Straight
Poles	5
Temperature Range - Operating	-25°C to +90°C
Wire Size AWG	18
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	30V AC / 36V DC
Material Info	
Engineering Number	WA5006-32
Reference - Drawing Numbers	
Sales Drawing	SD-120085-002-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained
ZZCERT_CE - Declaration of Conformity	CER_4000380999_00_000.pdf

Search Parts in this Series

120085 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION