

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1212110032](#)  
**Status:** **Active**  
**Overview:** mPm DIN Valve Connectors  
**Description:** mPm DIN Valve Connector, Form C - Micro 9.4mm, External Threads, 2 Pole Plus Ground with C4 Circuit, 24V, Yellow LED + VDR, Transparent, Profiled NBR Gasket, Single Bag, Unmounted

**Documents:**

|   |   |
|---|---|
| <a href="#">Drawing (PDF)</a>                                 | <a href="#">Product Specification STR-1299-001 (PDF)</a>        |
| <a href="#">Product Specification PS-121201-001-001 (PDF)</a> | <a href="#">Packaging Specification PK-121211-S29-001 (PDF)</a> |
| <a href="#">Product Specification STR-1251-001 (PDF)</a>      | <a href="#">RoHS Certificate of Compliance (PDF)</a>            |



**General**

|                    |  |
|--------------------|--|
| Product Family     | Field Attachable / Accessories           |
| Series             | <a href="#">121211</a>                   |
| Form               | C - Micro 9.4mm                          |
| IP Rating          | IP67                                     |
| Material - Contact | Brass                                    |
| Overview           | <a href="#">mPm DIN Valve Connectors</a> |
| Product Name       | mPm                                      |
| Type               | Field Attachable Connector               |
| UPC                | 884982530843                             |

**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Cable Diameter                | 3.00-5.50mm     |
| Coupling Type                 | External Thread |
| Diagnostics / LEDs            | Yes             |
| Diagnostics Port              | No              |
| Gender                        | N/A             |
| Keyway                        | None            |
| Material - Connector Body     | Polyamide       |
| Material - Coupling Nut       | N/A             |
| Material - Plating Mating     | Silver          |
| Net Weight                    | 15.103/g        |
| Orientation                   | 90° Angle       |
| Pitch - Mating Interface      | 9.40mm          |
| Poles                         | 2               |
| Temperature Range - Operating | -40°C to +90°C  |
| Wire Size AWG                 | 18              |

**Electrical**

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 16.0A |
| Voltage - Maximum             | 24V   |

**Material Info**

|                    |              |
|--------------------|--------------|
| Engineering Number | S29200TC420T |
|--------------------|--------------|

**Reference - Drawing Numbers**

|                         |   |
|-------------------------|---|
| Packaging Specification | PK-121211-S29-001                             |
| Product Specification   | PS-121201-001-001, STR-1251-001, STR-1299-001 |
| Sales Drawing           | SD-121211-001-001                             |

**EU ELV**

**Not Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Compliant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[121211 Series](#)