

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1502120017](#)  
**Status:** **Active**  
**Overview:** Ditto Wire-to-Wire Interconnects  
**Description:** Ditto Terminal Position Assurance (TPA), 3.00mm Pitch, 7 Circuits, High-Temperature, Black

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification 1502000000-TS-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification 1502000000-AS-000 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Packaging Specification PK-150212-0000-000 (PDF)</a>
<a href="#">Product Specification 1502000000-PS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Accessories
Series	<a href="#">150212</a>
Component Type	Terminal Position Assurance
Overview	<a href="#">Ditto Wire-to-Wire Interconnects</a>
Product Name	Ditto
UPC	191130502165

**Physical**

Circuits (Loaded)	7
Circuits (maximum)	7
Color - Resin	Black
Material - Resin	Nylon
Net Weight	0.397/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +150°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	1502000000-AS-000
Packaging Specification	PK-150212-0000-000
Product Specification	1502000000-PS-000, 1502000000-TS-000
Sales Drawing	1502120010-SD-000



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[150212 Series](#)

**Use With**

Ditto High-Temperature Hermaphroditic  
Crimp Housing [1502010017](#)