

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5015714007](#)
Status: **Active**
Overview: Pico-Clasp Wire-to-Board Connectors
Description: 1.00mm Pitch, Pico-Clasp PCB Header, Dual Row, Right-Angle, Surface Mount, 0.10µm Gold Plated, Inner Positive Lock, 40 Circuits, Natural

Documents:

2D Drawing (DXF)	Product Specification 5011891000-PS-001 (PDF)
2D Drawing DXF (PDF)	Product Specification 5011891000-PS-CHI-001 (PDF)
3D Model	Product Specification 5011891000-PS-JAP-001 (PDF)
3D Model (PDF)	Application Specification 5011890000-AS-000 (PDF)
Drawing (PDF)	Packaging Specification 5015719200-SPK-200 (PDF)
Product Specification 5011890000-PS-001 (PDF)	RoHS Certificate of Compliance (PDF)

General


Product Family	PCB Headers
Series	501571
Application	Signal, Wire-to-Board
Overview	Pico-Clasp Wire-to-Board Connectors
Product Name	Pico-Clasp
UPC	822348828388

Physical

Breakaway	No
Circuits (Loaded)	40
Circuits (maximum)	40
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Nylon
Net Weight	1084.000/mg
Number of Rows	2
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.102µm
Plating min - Termination	0.102µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	100V AC (RMS)/DC



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[501571](#) Series

Mates With

Pico-Clasp Female Housing [501189](#)

Material Info

Reference - Drawing Numbers

Application Specification	5011890000-AS-000
Packaging Specification	5015719200-SPK-200
Product Specification	5011890000-PS-001, 5011891000-PS-001, 5011891000-PS-CHI-001, 5011891000-PS-JAP-001
Sales Drawing	5015710000-SD-000

This document was generated on 01/17/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION