

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0009501091

Status:

Active

Overview:

SPOX Connector System

Description:

3.96mm Pitch SPOX Crimp Housing, Female, with Friction Ramp, 9 Circuits, Natural



Series image - Reference only

Documents:	
Drawing (PDF)	Product Specification PS-5195-005-001 (PDF)
3D Model (PDF)	Product Specification PS-5273-003-001 (PDF)
3D Model	Product Specification PS-5273-004-001 (PDF)
Product Specification PS-5195-003-001 (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	5195
Application	Signal, Wire-to-Board
Overview	SPOX Connector System
Product Name	SPOX
UPC	800753692619
Physical	
Circuits (maximum)	9
Color - Resin	Natural
Flammability	94V-2
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Nylon
Net Weight	2510.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Stackable	No
Temperature Range - Operating	-40° to +105°C
Material Info	
Engineering Number	5195-09
Reference - Drawing Numbers	
Product Specification	PS-5195-003-001, PS-5195-005-001, PS-5273-003-001, PS-5273-004-001
Sales Drawing	SD-5195-N-020

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

5195 Series

Mates With

5272 , 5273 , 5274 , 5096 , 53405 , 5271

Use With

5194

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION