

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5601251200](#)
Status: **Active**
Overview: [DuraClik Connector System](#)
Description: DuraClik ISL Wire-to-Board Terminal Position Assurance (TPA) Retainer, 12 Circuits, Gray

Documents:

Drawing (PDF)	Application Specification AS-560123-001-001 (PDF)
3D Model (PDF)	Packaging Specification PK-560125-001-001 (PDF)
3D Model	Datasheet (PDF)
Product Specification PS-560123-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-560123-003-001 (PDF)	

General

Product Family	Accessories
Series	560125
Application	Automotive
Component Type	Terminal Position Assurance
Overview	DuraClik Connector System
Product Name	DuraClik
UPC	889056359917


Physical

Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Gray
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	0.124/g
Number of Rows	1
Packaging Type	Bag
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +130°C

Material Info

Reference - Drawing Numbers

Application Specification	AS-560123-001-001
Packaging Specification	PK-560125-001-001
Product Specification	PS-560123-001-001, PS-560123-003-001
Sales Drawing	SD-560125-007-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[560125](#) Series

Use With

DuraClik ISL Terminal Housing [5601231200](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION