

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0701070039

Status:

Active

Overview:

Description:

SL Wire-to-Wire Panel Mount Crimp Housing, Single Row, Version B, with Mounting Ears, 5 Circuits, Black

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Crimp Housings

Series

70107

Application

Signal, Wire-to-Wire

Comments

Version B with Mounting Ears

Overview

sl_connectors

Product Name

SL

UPC

800753560864

Physical

Circuits (maximum)

5

Color - Resin

Black

Flammability

94V-0

Gender

Plug

Glow-Wire Capable

No

Lock to Mating Part

None

Material - Resin

Polyester

Net Weight

1.439/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

Yes

Pitch - Mating Interface

2.54mm

Polarized to Mating Part

Yes

Stackable

No

Temperature Range - Operating

-40° to +105°C

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Reference - Drawing Numbers

Packaging Specification

PK-70107-100-001

Product Specification

PS-70400-001

Sales Drawing

SD-70107-0036-0059-001, SD-70107-0036-0059-002, SD-70107-0036-0059-003

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[70107](#) Series

Mates With

SL Crimp Housing Versions A, G and D Only
[70066](#) (Version C and H will not mate to the 70107 housing series) . SL Insulation Displacement Connector Assembly, Version G Housing [70400](#) . SL Single Row Receptacle, Version G [70430](#)

Use With

[70021](#) SL Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION