

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0731000207

Status:

Active

Overview:

SMB RF Connectors

Description:

50 Ohms, SMB PCB Jack Receptacle

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-73598-0099-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Overview

Product Name

Style

Type

UPC

Wire/Cable Type

RF/Coax Connectors

73404

SMB RF Connectors

SMB

PCB

Subminiature

800753680753

N/A

Physical

Gender

Keying to Mating Part

Net Weight

Orientation

PCB Mounting

PCB Thickness - Recommended

Packaging Type

Panel Mount

Panel Mount Method

Reverse Polar

Jack

None

0.617/g

Straight

Through Hole

3.20mm

Tray

No

N/A

No

Electrical

Frequency

Impedance

Power / Voltage

4 GHz

50Ω

VOLTAGE: 335 Vrms@Sea Level

Solder Process Data

Duration at Max. Process Temperature (seconds)

Lead-freeProcess Capability

Max. Cycles at Max. Process Temperature

Process Temperature max. C

010

SMC&WAVE

002

260

Material Info


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-73598-0099-001

SD-73100-0207-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2021)4569-DC (8 July 2021)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit Contact US

China ROHS

ELV

RoHS Phthalates

50 Image

Not Relevant

Not Contained

Search Parts in this Series

73404 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION