

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0797581021

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead Sherlock Female-to-Sherlock Female, Tin (Sn) Plating, 300.00mm Length, 26 AWG, Black



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Datasheet \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	79758
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Sherlock Crimp Terminals
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	Sherlock
UPC	889056818674
Physical	
Cable Length	300.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.745/g
Packaging Type	Bag
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Size AWG	26
Wire/Cable Type	UL 1061
Material Info	
Reference - Drawing Numbers	
Sales Drawing	2012341212-000

EU ELV Not Relevant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021) Halogen-Free Status Not Low-Halogen	China RoHS
For more information, please visit Contact US	
China ROHS ELV RoHS Phthalates	Green Image Not Relevant Not Contained

Search Parts in this Series

79758 Series

Use With

Sherlock Crimp Housings [35507](#) , [35585](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION