

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190740009](#)
Status: **Active**
Overview: [Solderless Terminals](#)
Description: Krimptite Steel Star Ring Tongue Terminal for 18-22 AWG Wire, Stud Size 6 (M3.5)

Documents:

3D Model	Product Specification PS-19902-011-001 (PDF)
3D Model (PDF)	Product Specification PS-19902-013-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	19074
Crimp Quality Equipment	Yes
Overview	Solderless Terminals
Product Name	Krimptite
Type	Ring
UPC	800755072730

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.465/g
Packaging Type	Bag
Stud Size	6 (M3.5)
Wire Size AWG	18, 20, 22

Material Info

Engineering Number	SRA-S-129-06
--------------------	--------------

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-013-001
-----------------------	------------------------------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
reaction mass of
2-ethylhexyl 10-
ethyl-4,4-dioct
Methylhexahydrophthalic
anhydride
Nonadecafluorodecanoic
acid (PFDA) and its
sodiu
Aluminosilicate
Refractory Ceramic
Fibres
Boric acid
diisohexyl phthalate
Terphenyl,
hydrogenated
2-(2H-Benzotriazol-2-
yl)-4-(tert-butyl)-6-
(sec-b
2-(2H-Benzotriazol-2-
yl)-4,6-
ditertpentylphenol
Dibutylbis(pentane-2,4-
dionato-O,O')tin
Disodium-octaborate
Dibutyltin-dichloride
1,2-
Benzenedicarboxylic
acid, bis(3-
methylbutyl)
Disodium 3,3'-[[1,1'-
Biphenyl]-4,4'-
Diylbis(Azo)
Octanoic acid,
2,2,3,3,4,4,5,5,6,6,7,7,8,8,8-
pen
Benzo(ghi)perylene

China RoHS

Dipentyl phthalate
Imidazolidine-2-thione
Phenanthrene
Dihexyl-phthalate
4-aminoazobenzene
Silicic acid (H₂Si₂O₅),
barium salt (1:1),
lead-
Cyanamide, lead(2+)
salt (1:1)
Lead titanium
zirconium oxide
Dioxobis(stearato)trilead
Tetralead-trioxide-
sulphate
Pentalead-tetraoxide-
sulphate
pyrochlore, antimony
lead yellow
Cadmium
Lead
Cadmium-sulphide
Cadmium-oxide
Diboron-trioxide
1,2-Dimethoxyethane
1,2-
Benzenedicarboxylic
acid, bis(2-
methoxyethyl
Pentazinc-chromate-
octahydroxide
Potassium
hydroxyoctaoxidizincatedichromate
bis(2-methoxyethyl)
ether
Boric acid, disodium
salt, hydrate
Tris(2-chloroethyl)
phosphate
Lead chromate
molybdate sulfate red
Lead chromate

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[19074 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	640031200

Crimp Head for the 640071200
AT-200 Pneumatic
Hand Tool

This document was generated on 02/04/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION