

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1110150200

Status:

Active

Overview:

HSAutoLink Interconnect Systems

Description:

HSAutoLink Cable Assembly, USCAR/USB TYPE A Receptacle-to-MINI-B Plug, 1.00m Length, Polarization A



Series image - Reference only

Documents:

[Drawing \(PDF\)](#)

[Product Specification PS-68800-001-001 \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	111015
Application	Automotive
Assembly Configuration	Dual Ended Connectors
Comments	USCAR-30 Compliant
Connector to Connector	USB Type A-to-Mini-B
Overview	HSAutoLink Interconnect Systems
Product Name	HSAutoLink USCAR/USB
UPC	883906510084
Physical	
Cable Length	1.0m
Circuits (Loaded)	N/A
Gender	Male-Female
Lock to Mating Part	Yes
Net Weight	59.314/g
Number of Rows	1
Single Ended	No
Wire/Cable Type	Round
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-68800-001-001
Sales Drawing	SD-111015-006-001

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

111015 Series

Mates With

49616 USCAR/USB Header

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION