

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1110192010

Status:

Active

Overview:

HSAutoLink Interconnect Systems

Description:

HSAutoLink Cable Assembly, LVDS MINI-B Plug-to-MINI-B Inline Receptacle, 0.50m Length, Polarization A-to-A



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Cable Assemblies
Series	111019
Application	Automotive
Assembly Configuration	Dual Ended Connectors
Connector to Connector	STP 100/PG Mini-B-to-Mini-B
Overview	HSAutoLink Interconnect Systems
Product Name	HSAutoLink LVDS
UPC	883906510268
Physical	
Cable Length	0.50m
Circuits (Loaded)	N/A
Gender	Male-Female
Lock to Mating Part	Yes
Net Weight	32.100/g
Number of Rows	1
Single Ended	No
Wire/Cable Type	Round
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-111019-2000-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

111019 Series

Mates With

49616 USCAR/USB Header

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION